

EKDMGN02B-KIT:

Chip Ferrite Beads for Noise Suppression (Small Case Size):

No.	QTY	MANUFACTURER'S PART NUMBER	Product Description	DESCRIPTION
1	20	BLF02RD331GNED	Ferrite Bead SMD	FB SMD 01005inch 330ohm NONAUTO
2	20	BLF02RD471GNED	Ferrite Bead SMD	FB SMD 01005inch 470ohm NONAUTO
3	20	BLF03JD421GNED	Ferrite Bead SMD	FB SMD 0201inch 420ohm NONAUTO
4	20	BLM03AX100SN1D	Ferrite Bead SMD	FB SMD 0201inch 10ohm NONAUTO
5	20	BLM03AX121SN1D	Ferrite Bead SMD	FB SMD 0201inch 120ohm NONAUTO
6	20	BLM03AX601SN1D	Ferrite Bead SMD	FB SMD 0201inch 600ohm NONAUTO
7	20	BLM03AX102SN1D	Ferrite Bead SMD	FB SMD 0201inch 1000ohm NONAUTO
8	20	BLM03BC330SN1D	Ferrite Bead SMD	FB SMD 0201inch 33ohm NONAUTO
9	20	BLM03BC560SN1D	Ferrite Bead SMD	FB SMD 0201inch 56ohm NONAUTO
10	20	BLM03BC800SN1D	Ferrite Bead SMD	FB SMD 0201inch 80ohm NONAUTO
11	20	BLM03EB250SN1D	Ferrite Bead SMD	FB SMD 0201inch 25ohm NONAUTO
12	20	BLM03EB500SN1D	Ferrite Bead SMD	FB SMD 0201inch 50ohm NONAUTO
13	20	BLM03HB191SN1D	Ferrite Bead SMD	FB SMD 0201inch 190ohm NONAUTO
14	20	BLM03HD331SN1D	Ferrite Bead SMD	FB SMD 0201inch 330ohm NONAUTO
15	20	BLM03HD601SN1D	Ferrite Bead SMD	FB SMD 0201inch 600ohm NONAUTO
16	20	BLM03HD102FN1D	Ferrite Bead SMD	FB SMD 0201inch 1000ohm NONAUTO
17	20	BLM03HD152FN1D	Ferrite Bead SMD	FB SMD 0201inch 1500ohm NONAUTO
18	20	BLM03HD182FN1D	Ferrite Bead SMD	FB SMD 0201inch 1800ohm NONAUTO
19	20	BLM03HD102SN1D	Ferrite Bead SMD	FB SMD 0201inch 1000ohm NONAUTO
20	20	BLM03PX220SN1D	Ferrite Bead SMD	FB SMD 0201inch 22ohm NONAUTO
21	20	BLM03PX330SN1D	Ferrite Bead SMD	FB SMD 0201inch 33ohm NONAUTO
22	20	BLM03PX800SN1D	Ferrite Bead SMD	FB SMD 0201inch 80ohm NONAUTO
23	20	BLM03PX121SN1D	Ferrite Bead SMD	FB SMD 0201inch 120ohm NONAUTO
24	20	BLM15AX300SN1D	Ferrite Bead SMD	FB SMD 0402inch 30ohm NONAUTO

25	20	BLM15AX700SN1D	Ferrite Bead SMD	FB SMD 0402inch 70ohm NONAUTO
26	20	BLM15AX121SN1D	Ferrite Bead SMD	FB SMD 0402inch 120ohm NONAUTO
27	20	BLM15AX221SN1D	Ferrite Bead SMD	FB SMD 0402inch 220ohm NONAUTO
28	20	BLM15AX601SN1D	Ferrite Bead SMD	FB SMD 0402inch 600ohm NONAUTO
29	20	BLM15AX102SN1D	Ferrite Bead SMD	FB SMD 0402inch 1000ohm NONAUTO
30	20	BLM15HD601SN1D	Ferrite Bead SMD	FB SMD 0402inch 600ohm NONAUTO
31	20	BLM15HD102SN1D	Ferrite Bead SMD	FB SMD 0402inch 1000ohm NONAUTO
32	20	BLM15HD182SN1D	Ferrite Bead SMD	FB SMD 0402inch 1800ohm NONAUTO
33	20	BLM15GG221SN1D	Ferrite Bead SMD	FB SMD 0402inch 220ohm NONAUTO
34	20	BLM15GG471SN1D	Ferrite Bead SMD	FB SMD 0402inch 470ohm NONAUTO
35	20	BLM15GA750SN1D	Ferrite Bead SMD	FB SMD 0402inch 75ohm NONAUTO
36	20	BLM15PX330SN1D	Ferrite Bead SMD	FB SMD 0402inch 33ohm NONAUTO
37	20	BLM15PX600SN1D	Ferrite Bead SMD	FB SMD 0402inch 60ohm NONAUTO
38	20	BLM15PX800SN1D	Ferrite Bead SMD	FB SMD 0402inch 80ohm NONAUTO
39	20	BLM15PX121SN1D	Ferrite Bead SMD	FB SMD 0402inch 120ohm NONAUTO
40	20	BLM15PX181SN1D	Ferrite Bead SMD	FB SMD 0402inch 180ohm NONAUTO
41	20	BLM15PX221SN1D	Ferrite Bead SMD	FB SMD 0402inch 220ohm NONAUTO
42	20	BLM15PX331SN1D	Ferrite Bead SMD	FB SMD 0402inch 330ohm NONAUTO
43	20	BLM15PX471SN1D	Ferrite Bead SMD	FB SMD 0402inch 470ohm NONAUTO
44	20	BLM15PX601SN1D	Ferrite Bead SMD	FB SMD 0402inch 600ohm NONAUTO
45	20	BLM15KD200SN1D	Ferrite Bead SMD	FB SMD 0402inch 20ohm NONAUTO
46	20	BLM15KD300SN1D	Ferrite Bead SMD	FB SMD 0402inch 30ohm NONAUTO
47	20	BLM15KD121SN1D	Ferrite Bead SMD	FB SMD 0402inch 120ohm NONAUTO