

# SPARE PARTS LIST

## MODEL NO. 9557NB

ITEM	PART NO.	DESCRIPTION	QTY	NOTE
001	621708-9	FIELD 240V 9556NB-9558NB&PB	1	240V
002	418770-1	BAFFLE PLATE 9556NB-9558NB/PB	1	
003	421868-5	LABYRINTH RUBBER RING 9553/955	1	
004	210034-7	BALL BEARING 607LLB 9553/9555N	1	
005	681636-0	INSULATION WASHER DP4003/4304 HR2432	1	
006	515613-9	ARMATURE ASS 240V 9556-58NB&PB INC. 4,5,7	1	240V
007	240076-7	FAN 56 9553-9558NB	1	
008	317821-6	GEAR HOUSING COVER 9553-9558NB	1	
009	213445-5	O-RING 26 MT952/9553-9555NB	1	
010	210042-8	BALL BEARING 629LLB GD0600	1	
011	227464-5	SPIRAL BEVEL GEAR 10 9553-9558	1	
012	252186-8	HEX NUT M6 9553-9558NB	1	
013	417771-6	PIN CAP MT952/9553-9558NB	1	
014	233376-2	*COMPRESSION SPRING 10PK	1	
015	266361-0	*R.H SQUARE NECK BOLT M8 10PK	4	
016	213960-9	O RING 5 9553-9558NB	1	
017	256486-8	SHOULDER PIN 4 9553-9558NB	1	
018	317814-3	GEAR HOUSING 9553-9558NB	1	
019	263002-9	RUBBER PIN 4/9402/HR160DWH/903HM1202C/BO3700	1	
020	210033-9	BALL BEARING 696ZZ 2107F/9553-9555NB	1	
021	961052-5	*EXT DIN 471 CIRCLIP-12 10PK	1	
022	267794-2	WAVE WASHER 12 9553-9558NB	1	
023	227465-3	SPIRAL BEVEL GEAR 37 9554/5NB	1	
024	962151-6	RETAINING RING R-32 8419B/2 95	1	
025	211129-9	BALL BEARING 6201DDW LS800DWB 9501B	1	
026	267238-2	*FLAT WASHER 12 MT952 10PK	1	
027	213622-9	O RING 45 9553-9558NB	1	
028	317819-3	BEARING BOX 9553-9558NB	1	
029	265099-4	PAN HD SCREW M4X14 9553-9555NB	4	
030	345464-4	LABYRINTH RING 9553-9558NB	1	
031	254011-9	*WOODRUFF KEY4-8 10PK	1	
032	324489-1	SPINDLE 9553-9555NB/57-58NB	1	
033	265103-9	*PH SCREW M5X14 MT952 10PK	1	
034	125267-0	WHEEL COVER ASSY 9554NB/57NB INC. 33	1	
035	224298-7	INNER FLANGE 42 9503BH/9005B/9	1	
036	224554-5	LOCKNUT 9541/9542/9522NB/9565	1	
037	266345-8	*TAPPING SCREW M4X80 10PK	2	
038	861255-0	NAME PLATE 9557NB	1	
039	266007-8	*PT SCREW 3X10 TRIBULAR 10PK	4	
040	643760-7	BRUSH HOLDER BO6040/9564&65CV	1	
041	194074-2	CARBON BRUSH CB-325 9553-9555	1	
042	418729-8	SPACER 9556NB-9558NB	1	
043	650560-8	SWITCH DPX-2110-R 9553-9555NB	1	
044	687124-5	STRAIN RELIEF MT240	1	
045	266326-2	*TAPPING SCREW M4X18 10PK	2	
046	645233-6	NOISE SUPPRESSOR 9553-9555NB	1	
047	682566-8	CORD GUARD 10 HR2020/2440/24509553NB/HR2432	1	
048	692527-0	LEAD WIRE HR4000C/HR2020/LF100	1	240V
049	419566-3	SWITCH KNOB 9553-9555NB	1	
050	418725-6	MOTOR HOUSING 9556NB-9558NB	1	
051	643760-7	BRUSH HOLDER BO6040/9564&65CV	1	
052	233121-5	*COMPRESSION SPRING 4 5PK	1	
053	418728-0	SWITCH LEVER B 9556NB-9558NB	1	
054	418726-4	REAR COVER 9553-9555NB	1	
055	266326-2	*TAPPING SCREW M4X18 10PK	1	
A01	153489-2	GRIP 36 COMP MT952/9553-9558NB	1	
A02	782421-5	LOCK NUT WRENCH 35 9554/5/7/8N	1	
A03	P-34665	DIAMOND BLADE 115MM PROMO	1	
E01	655030-2	*PLUG UK TYPE 2107F/JR3050T HM1810/HR2432/JR3060T/3070CT	1	115V

# SPARE PARTS LIST

---

PAGE 2

MODEL NO. 9557NB

ITEM	PART NO.	DESCRIPTION	QTY	NOTE
E02	654091-9	NON INSULATED TERMINAL LC1230 N910/RP0910/HM1810/HR2432/JR301 15V		

---

# SERVICE DRAWING

MODEL NO. 9557NB

