



## Main

Device short name	LA9G
Product or Component Type	Spreader
Accessory / separate part category	Connection accessories
Range compatibility	TeSys LC1G TeSys LR9G
Poles description	3P
Quantity per Set	Set of 3

## Complementary

Net Weight	3.17 lb(US) (1.44 kg)
Product Compatibility	LC1G630...800
Height	5.31 in (135 mm)
Width	2.99 in (76 mm)
Depth	1.30 in (33 mm)

## Environment

Pollution degree	3 IEC 60947-1
Product Certifications	UL
Standards	EN/IEC 60947-1 UL 60947-1 CSA C22.2 No 60947-1 GB/T 14048
Ambient Air Temperature for Operation	-40...140 °F (-40...60 °C)
Ambient Air Temperature for Storage	-76...176 °F (-60...80 °C)
Operating altitude	9842.52 ft (3000 m) without derating 5000 m with derating factor

## Ordering and shipping details

Category	22328-TESYS GIGA ACCESSORIES
Discount Schedule	I12
GTIN	3606481916648
Returnability	Yes

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1.57 in (4.0 cm)
Package 1 Width	3.94 in (10.0 cm)
Package 1 Length	7.87 in (20.0 cm)
Package 1 Weight	3.43 lb(US) (1.556 kg)
Unit Type of Package 2	S02
Number of Units in Package 2	4
Package 2 Height	5.91 in (15.0 cm)

Package 2 Width	11.81 in (30.0 cm)
Package 2 Length	15.75 in (40.0 cm)
Package 2 Weight	14.75 lb(US) (6.692 kg)

### Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Styrene, which is known to the State of California to cause cancer, and Bisphenol A (BPA), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End Of Life Information</a>
PVC free	Yes
Halogen content performance	Halogen free plastic parts product