

Check Stock/Pricing by Product No.

Search By Size and Type

Find a Distributor / Rep

[Home](#) / [Products](#) / [General Use Boxes](#) / [Rack Mount Aluminum Chassis Series](#) / Rack Mount Aluminum Chassis RM-14212

Rack Mount Aluminum Chassis RM-14212



Model # RM-14212

[Rack Mount Aluminum Chassis Series](#)

- Side Panel mounting holes are punched on 0.87-inch grid to allow total flexibility in mounting of components
- Rear Panel is fully adjustable from front to rear
- Standard 19.00-inch Front Panels feature “Surface Shield” protection which provides surface for laying out drilling and punching positions
- Front Panel: 0.12-inch thick mill finish aluminum with “Surface Shield” protection.
- Side & Rear Panels: 0.09-inch aluminum
- Other finishes available on request
- Shipped unassembled with all necessary assembly hardware
- Supports 25 lb. equipment load (50 lb. with optional rear mounting brackets)

Compare Sizes and Models

[See Accessories](#)

[Request Modifications](#)

Check Stock / Pricing

External Size H x W x D: 5.25" x 19.00" x 17.06"

Internal Size H x W x D: 5.12" x 16.82" x 16.97"


Weight: 4.25 lbs

Color: Natural

Ventilated: Ventilated



DRAWING



To learn more about aluminum enclosures visit <http://www.budind.com/>

OTHER MODELS IN THIS SERIES

-- External Dimensions --

-- Internal Dimensions --

Model #	External Dimensions	Internal Dimensions
RM-14296	5.25" x 18.00" x 26.00"	5.07" x 18.82" x 25.82"



Help

Model #	External Dimensions	Internal Dimensions ⓘ
RM-14212	5.25" x 19.00" x 17.06"	5.12" x 16.82" x 16.97"
RM-14222	5.25" x 19.00" x 22.00"	5.12" x 16.82" x 21.78"
RM-14292	5.25" x 19.00" x 24.00"	5.07" x 18.82" x 23.82"
RM-14213	7.00" x 19.00" x 17.06"	6.87" x 16.82" x 16.97"
RM-14223	7.00" x 19.00" x 22.00"	6.87" x 16.82" x 21.78"
RM-14293	7.00" x 19.00" x 24.00"	6.82" x 18.82" x 23.82"
RM-14297	7.00" x 19.00" x 26.00"	6.82" x 18.82" x 25.82"
RM-14214	8.75" x 19.00" x 17.06"	8.62" x 16.82" x 16.97"
RM-14224	8.75" x 19.00" x 22.00"	8.62" x 16.82" x 21.78"
RM-14294	8.75" x 19.00" x 24.00"	8.57" x 18.82" x 23.82"
RM-14298	8.75" x 19.00" x 26.00"	8.57" x 18.82" x 25.82"
RM-14215	10.50" x 19.00" x 17.06"	10.37" x 16.82" x 16.97"
RM-14225	10.50" x 19.00" x 22.00"	10.37" x 16.82" x 21.78"
RM-14295	10.50" x 19.00" x 24.00"	10.32" x 18.82" x 23.82"
RM-14299	10.50" x 19.00" x 26.00"	10.32" x 18.82" x 25.82"

ACCESSORIES



Series Photo

Internal Chassis C-14242

C-14242

[View Details](#)

Check Stock / Pricing

Solid Top or Bottom Cover TBC-14252

TBC-14252

[View Details](#)

Check Stock / Pricing

Ventilated Top or Botto 14262

TBC-14262

[View Details](#)

Check Stock /

RELATED PRODUCT SERIES



Aluminum Chassis Series

VIEW SERIES DETAILS