

Digital Microscope

Selection Guide





Advantages of Digital Microscopes

Ultra Sharp Digital Magnification

Microscope technology has rapidly advanced over the years. Today's digital microscopes can magnify smaller objects better than ever before. Digital microscopy camera technology enables you to inspect any object, small or large, in ultra sharp digital magnification. With digital microscopes, lenses and positioning are becoming increasingly better. Although it is not as vivid as the 3 dimensional imagery stereo microscopes offer, the 2 dimensional image that is projected onto monitors has become very comparable with the advancement of technology. Accessories like tilt tables and LED lighting help the 2D image on screen become more vivid and appear more 3 dimensional.

USB and HDMI Outputs

Digital microscopes take the technology even further with microscope cameras and the integration of USB capabilities. Live snapshots can now be taken and saved to an inserted USB memory stick or the internal storage of the microscope for quick access. Saving an image to internal storage makes it easy to access for later inspection or to share inspection images with others not in the lab or office.

Ergonomically Designed for Ease of Use

Working with digital microscopes can reduce overall inspection time. With the image being projected onto a monitor, there is no more neck or eye strain from bending down and looking through binocular lenses, giving ease to long term usage.

Having the image magnified onto a screen also allows multiple viewers at the same time which helps improve collaboration and teaching techniques.

Versatile Accessories

Most digital microscopes come with a variety of accessories to enhance inspection for specific projects. Accessories can range from different attachable mounts to creating a variety of angles and working distances with different table pieces. LED lighting accessories also minimizes shadows and hidden elements below the microscope to help with focusing and catching the object at different views.





Digital vs Stereo

The Breakdown

Features	Digital Microscope	Stereo Zoom Microscope		
Ergonomic	✓			
3D Image		✓		
Image Depth		✓		
Image Capture	✓	Selected Few		
Measure	✓	Selected Few		
Price Range	\$224 - 5,204	\$994 - 4,543		



Mighty Cam Pro

Auto Focus Inspection System



Item #26100-258

- 1080p Full HD Imaging at 60 FPS
- USB+HDMI Outputs and SD Card Port
- Built-in measurement software No PC required
- Advanced measurement software included for computer connectivity
- Achieve instant auto focus
- Enhances productivity eliminates eye strain and body fatigue
- Save high resolution image/video files directly to SD card

















Item #26700-121-PRO

- Superior optics: 7x-70x magnification at a 6 inch working distance
- Achieve instant auto focus no need to adjust the focus of the lens
- Ultimate flexibility: 18 inch flexible arm with a 360 ball joint provides limitless positioning options
- Crystal clear viewing: 22 inch 1080p monitor
- No computer required for image processing
- LED ring light with 96 ultra-bright, adjustable LEDs
- Eliminates the fatigue and eye strain associated with frequent microscope use

Aven offers many different Mighty Cam PRO systems!

To explore our Mighty Cam PRO bundles visit our website www.aventools.com





MicroVue

All-In-One Digital Microscope



Item #26700-140

- Built-in 11.6" monitor for ergonomic viewing
- 17x 110x magnification (on the built-in monitor)
- HDMI output for external monitor viewing Built-in measurement capabilities
- Save image/video files to USB storage device (USB included)
- Compact design saves bench top space

MicroVue Accessories



2X Auxiliary Lens #26700-140-L20X

- 34.4x 221x Magnification
- Metal Ring with glass lens
- Easy screw in installation



0.5X Auxiliary Lens #26700-140-L05X

- 8.6x 55.2x Magnification
- Metal Ring with glass lens
- Easy screw in installation




Focus Mount Arbor #26700-140-M32

Designed to enhance the versatility of the MicroVue Digital Microscope, this Focus Mount with Arbor allows operators to connect the MicroVue to a boom stand. Boom stands are ideal for scanning over larger objects, a feature not available with standard post stands



Cyclops


Digital Microscope



Item #26700-423

- Magnification 13x-140x on a 24" monitor
- Working Distance 22mm to 214mm
- 2M CMOS Sensor
- Full HD 1080P signal output at 60 frames per second
- USB 3.0 Type C high speed transmission
- Application software with support for Windows and MAC
- Image and Video Capture, measurement etc. with included software

BEST FOR: laboratory use, Industrial Inspection, quality control, life sciences, and green technology



Item #26700-401

- Magnification ranges up to 132x on a 21.5" HD monitor.
- 2-Megapixel sensor provides operators with exceptionally crisp, high resolution images.
- Articulating Arm Stands available in 17-inch and 12-inch models.
- 10x Objective lens available for purchase offering up to 960x magnification.
- Auto focus within range
- IR remote control
- HDMI output to allow connection to HD monitor *no computer required*

BEST FOR: laboratory use, Industrial Inspection, quality control, life sciences, and green technology

Cyclops Accessories



18" Flex Arm #26800B-558

- 360° Swivel head and magnetic base
- Tilt, rotate and position
- 1/4" Screw mount



Articulating Arm #26800B-553

- 17.7" Post 16.3" articulating arm
- Heavy Duty Clamp



Cyclops Objective Lens 4x w/ Polarizer #26700-400-PL01

- Helps reduce glare and reflection
- 4x Magnification



Cyclops 4x Long Focus Lens #26700-400-L-4XLF

- 4x Long Lens offers higher magnification at the same working distance



Cyclops Objective Lens 4x #26700-400-L4X

- Replacement lens to increase magnification 4x



Cyclops Objective Lens 10x #26700-400-L10X

- Optional lens addition to increase magnification 10x



Mighty Scope v2

Digital Microscope




Item #26700-218

- Magnification 10x-50x optical and up to 200x digital
- Portable / Hand-held
- Easy plug-and-play USB connection
- Built in LED lighting
- Customize with various stands and lighting arrangements
- MicroViewer Plus Software

BEST FOR: engineers, scientists, doctors, lab techs, forensic examiners, educators and more

Mighty Scope Bundles & Accessories



Mighty Scope v2 w/ Diffuser Item #26700-218-DFS

- The diffuser can be attached to the Mighty Scope to evenly spread light for shadow-free illumination on shiny objects



With Diffuser



Without Diffuser



With Polarizer



Mighty Scope v2 w/ Polarizer Item #26700-218-PLR

- This polarizer helps to reduce glare and hot spots from highly reflective surfaces while also enhancing contrast





Without Polarizer



Diffuser Attachment for Mighty Scope v2 #26700-218-DIFF



Polarizer Attachment for Mighty Scope v2 #26700-219



Mighty Scope ClearVue

All-In-One Digital Microscope



Item #26700-220-MNT

- Compact All-in-one system
- 8x-25x Magnification
- 1080p Full HD Imaging at 60 FPS
- Rechargeable Battery
- HDMI Output for additional monitor viewing
- ezlmageX3 software included
- Enhances productivity eliminates eye strain and body fatigue
- 5" Built-in HD screen
- Save high resolution image/video files directly to microSD card
- 1080p Full HD Output



Item #26700-220-505

- Compact All-in-one system
- Flexible LED Illumination
- Dual 14.5" Gooseneck LEDs (ideal when reflections from shiny objects need to be eliminated)
- Back-light (ideal for observing transparent objects)
- 8x-25x Magnification
- 1080p Full HD Imaging at 60 FPS
- Rechargeable Battery
- HDMI Output for additional monitor viewing
- ezlmageX3 software included
- Enhances productivity eliminates eye strain and body fatigue
- 5" Built-in HD screen
- Save high resolution image/video files directly to microSD card
- 1080p Full HD Output





ClearVue Accessories



Post Stand For Mighty Scope ClearVue #26700-220-STN

- 9" Post stand with an 8.6" x 7" base
- Features fine focus adjustment for precise focusing
- Can be adjusted to inspect objects large and small



ClearVue w/ Dual Gooseneck LEDs and Backlight

#26700-220-505

- Flexible Illumination
- -14.5" Dual Gooseneck LEDs
- Back-Light



ClearVue on 34" Spring Balanced Arm w/ Table Clamp #26700-220-559

- The arm can be raised, lowered, and tilted as needed
- Allows the ClearVue to be swiveled out of the way when not in use



ClearVue on 18" Flex Arm Stand w/ Table Clamp #26700-220-557

- Can be flexed and bent to any position
- At the end of the stand is a 360 ball joint with a screw lock providing 360 degrees of rotation



ClearVue on 18" FlexArm Stand w/ Magnetic Base

#26700-220-558

- Can be flexed and bent to any position
- At the end of the stand is a 360 ball joint with a screw lock providing 360 degrees of rotation
- 3" Magnetic base can be mounted to metal surfaces



ClearVue on Adjustable Spring Balanced Arm w/ Weighted Base #26700-220-559WB

- Can be raised, lowered and tilted as needed
- Allows the ClearVue to be swiveled out of the way when not in use
- Can be placed anywhere on the work surface



Compact Gliding Stage X/Y/R #26800B-479

- Compact and Convenient
- The stage smoothly glides horizontally and vertically
- The rotating stage provides 360 degrees of rotation



Optional Configurations

- The Mighty Scope ClearVue can be configured with optional stands to increase working distance, flexibility, and enhance your workspace



3D Viewer Systems

Digital Microscopes w/3D Viewer



Mighty Cam ES on Track Stand [22x - 147x]

Item #26700-151-C05-259-506

- 0.6x to 4x Zoom magnification
- Detented Lens for High Accuracy Measurement
- HD camera with both HDMI and USB outputs with Advanced Measurement Software
- 3D viewing with included attachment
- Track Stand with Large Base (adjustable overhead & back light)
- Save high resolution image/video files directly to microSD card
- 1080p Full HD Output



Mighty Cam ES on Post Stand w/ Gooseneck LEDs [22x - 147x]

Item #26700-151-C05-259-570

- 0.6x to 4x Zoom magnification
- Detented Lens for High Accuracy Measurement
- HD camera with both HDMI and USB outputs with Advanced Measurement Software
- 3D viewing with included attachment
- Heavy-duty post stand
- Flexible gooseneck LEDs with brightness adjustment
- LEDs can be positioned where needed for optimal illumination



Mighty Cam Eidos on Track Stand [13x - 94.4x]

Item #26700-151-C05-260-506

- 0.6x to 4x zoom magnification, detented Lens for High Accuracy Measurement
- 3D viewing with included attachment
- Track Stand with Large Base (adjustable overhead & back light)
- All-in-one, compact system w/ built-in measurement software No PC required
- 1080p Full HD Imaging at 60 FPS
- HDMI Output for additional monitor viewing
- Save high resolution image/video files directly to USB Storage card
- 11.6" built-in HD monitor can be tilted to the optimal viewing angle



Mighty Cam Eidos on Post Stand w/ Gooseneck LEDs [13x - 94.4x] Item #26700-151-C05-260-570

- 0.6x to 4x zoom magnification, detented Lens for High Accuracy Measurement
- 3D viewing with included attachment
- Heavy-duty post stand with adjustable LEDs
- All-in-one, compact system w/built-in measurement software No PC required
- 1080p Full HD Imaging at 60 FPS
- HDMI Output for additional monitor viewing
- Save high resolution image/video files directly to USB Storage card
- 11.6" built-in HD monitor can be tilted to the optimal viewing angle



Mighty Cam ES

Streamlined USB + HDMI Camera



Mighty Cam ES w/ USB + HDMI Outputs & SD Card Port Item #26100-259

- Streamlined camera designed for efficient inspection
- USB + HDMI outputs view on an HD monitor or from your PC
- SD Card (save images and video files)
- Compatible with C C/S Mount lenses and trinocular microscopes
- 1/4-20" screw mount adapter mounts to nearly any camera stand
- Advanced measurement software included for use in PC mode

Mighty Cam ES Systems



Mighty Cam ES [7x-70x] Macro Lens w/ Ultra Glide Stand #258-181-556-ES

- 7x 70x magnification at a 6 inch working distance
- Includes Aven's Dual Gooseneck LED Task Light
- Ultra Glide Arm Stand (easily move across a specimen)



Mighty Cam ES [7x-70x] Macro Lens w/ Post Stand #258-207-570-ES

- 7x 70x magnification at a 6 inch working distance
- Includes Aven's Focus mount with built-in LED ring light
- LED Ring Light is built into the focus mount to ensure that it is secure and will not come loose



Mighty Cam ES [7x-70x] Macro Lens w/Double Arm Boom Stand #258-209-534-ES

- -7x 70x magnification at a 6 inch working distance
- Includes Aven's Focus Mount with built-in LED ring light
- LED Ring Light is built into the focus mount to ensure that it is secure and will not come loose
- Double Arm Boom Stand (easily move across a specimen)



Mighty Cam ES [3x-43x] Macro Lens w/Post Stand #26700-108-ES

- 3x 43x magnification
- -Includes heavy duty post stand to accommodate a large variety of parts
- Includes an LED ring light that provides uniformity & shadow free illumination



Mighty Cam ES [28.8x-384x] Micro Lens w/Standard Stand #26700-109-ES

- 57.6x 384x (28.8x 192x when using the 0.5x objective lens)
- -Includes heavy duty post stand to accommodate a large variety of parts
- Includes an LED ring light that provides uniformity & shadow free illumination



Mighty Cam ES [7x-70x] Macro Lens w/FlexArm Stand #26700-121-ES

- 7x 70x magnification at a 6 inch working distance
- 18 inch flexible arm with a 360 ball joint provides limitless positioning options
- Includes an LED ring light with 96 ultrabright, adjustable LEDs



Digital Microscope Table

Product	Magnification	Software	USB Output	HDMI Output	Built-in Screen	Image/Video Capture
MicroVue	17x - 110x	Internal Software	For USB mouse & Flash Drive Only	√	√	Via Software/ USB Storage
Mighty Cam Pro	N/A	Internal Software/ Capture Software	✓	✓		Via Software/ SD Card
Mighty Cam USB	N/A	Capture Software	✓			Via Software
Mighty Cam ES	N/A	Internal Software/ Capture Software	✓	✓		Via Software/ SD Card
Cyclops 3.0	13x - 140x	UM Viewer	✓	✓		Via Software
Cyclops HDMI	13x - 132x	N/A		✓		No
Mighty Cam Eidos	N/A	Internal Software	For USB Mouse & Flash Drive Only	√	√	Via Software/ USB Storage
Mighty Scope v2	10x-50x Optical 200x Digital	MicroViewer Plus	✓			Via Software
Mighty Scope Clear Vue	8x - 25x	Internal Software/ ezImageX3	✓	✓	√	Via Software/ MicroSD card

Contact US

4330 Varsity Dr, Ann Arbor, MI 48108

sales@aventools.com

www.AvenTools.com

Phone: 734-973-0099