Electrician Scissors & Blades

Multi-Purpose Electrician Scissors Kit with Electrician Scissors and Cable Stripping Blade



11010

Multi-Purpose Electrician Scissors

- These 2" scissor blades are made from high tensile stainless steel, providing excellent strength and performance
- Designed for cutting/stripping soft cable and wires
- Light, strong and comfortable handles are made from impact-resistant plastic

Cable Stripping Blade

- The 2" blade is made from stainless steel and is designed for stripping wires and cables
- Features a protective blade cover, which includes a groove to aid in stripping cables
- Designed to work with cables with an external diameter of 3.0mm - 30.0mm

Product ID	Description
11010	Multipurpose Electrician Scissors Kit W/ Scissors and Knife
11015	Electrician Cable Stripping Knife W/ Blade Protector
11011	Multipurpose Electrician Scissors W/ Wire Stripper

Electrician Scissors with Wire Stripping Slots & Plastic Grips



11013

Electrician Scissors with Wire Stripping Slots & Plastic Grips

- 2" stainless steel Blade designed for stripping wires and cables
- Hardened stainless steel blades for durability and rust free operation
- Features a protective blade cover, includes groove to aid in stripping cables
- Has two notches for stripping 19 AWG and 23 AWG copper wires
- Designed to work with cables with an external diameter of 3.0mm - 30.0mm
- Built in scraper for shaving thin cables
- Ergonomic comfort grips

Product ID	Description
11013	Electrician Scissors W/ Wire Stripping Slots & Plastic Grips





Scissors & Hemostats

5" Electrician Scissor

- Fully polished stainless steel provides excellent corrosion resistance
- Scraper and file on back edge of the blade
- Notched to strip 23-19 AWG wire



11012

Product ID	Description
11012	5" Electrician Scissor

4-1/2" Precision Scissor

- Fully polished stainless steel provides excellent corrosion resistance
- Fine beaks for precise and delicate work
- 1-3/8" durable stainless steel blade



11016

Product ID	Description
11016	4-1/2" Precision Scissor

4-1/2" Slim Blade Straight Scissor

- Fully polished stainless steel provides excellent corrosion resistance
- Precision scissor for general use and cutting fine wire
- 1-1/4" durable stainless steel blade



11014

Product ID	Description
11014	4-1/2" Slim Blade Straight Scissor

8" All Purpose Standard Scissor

- Fully polished stainless steel provides excellent corrosion resistance
- 3-3/4" durable stainless steel blade



11023

Product ID	Description
11023	8" All Purpose Standard Scissor

Hemostat - Straight

- Manufactured from 400 series stainless steel
- Mirror polished to provide excellent corrosion resistance
- Serrated jaws hold objects firmly without cutting them
- Designed for intricate work in tight spaces
- Ratchet lock in handle allows varying gripping pressure



12001

Product ID	Description	Jaw Length
12001	Hemostat - Straight | 3.5in	20mm
12015	Hemostat - Straight | 5in	25.4mm
12011	Hemostat - Straight | 5in w/Plastic Coated Handle	25.4mm
12017	Hemostat - Straight | 6in	31.75mm
12013	Hemostat - Straight | 6in w/Plastic Coated Handle	31.75mm
12019	Hemostat - Straight | 8in	60mm
12030	Hemostat - Straight | 18in	139mm
12032	Hemostat - Straight | 24in	155mm

Hemostat - Curved

- Manufactured from 400 series stainless steel
- Mirror polished to provide excellent corrosion resistance
- Serrated jaws hold objects firmly without cutting them
- Designed for intricate work in tight spaces
- Ratchet lock in handle allows varying gripping pressure



12002

Product ID	Description	Jaw Length
12002	Hemostat - Curved | 3.5in	20mm
12016	Hemostat - Curved | 5in	25.4mm
12012	Hemostat - Curved | 5in w/Plastic Coated Handle	25.4mm
12018	Hemostat - Curved | 6in	31.75mm
12014	Hemostat - Curved | 6in w/Plastic Coated Handle	31.75mm
12020	Hemostat - Curved | 8in	60mm
12031	Hemostat - Curved | 18in	139mm
12033	Hemostat - Curved | 24in	155mm

Alligator Clamp

- Serrated jaws for secure grip
- Angled to provide maximum view
- Stainless steel construction
- Designed to securely retrieve and hold small parts



12201

Product ID	Description	Jaw Length	Opening
12201	Alligator Clamp 3.5"	0.5"	0.25"
12202	Alligator Clamp 5.5"	0.5"	0.25"

Probes

Probe Straight Needle Point

- Manufactured from 400 series stainless steel
- Excellent corrosion resistance
- Sharp tip for precision work around delicate circuits and components
- Single end straight tip
- Eight sided handle to ensure grip and prevent rolling



20031

Product ID	Description
20031	Probe Straight Needle Point

Probe Double Sided Scraper Bent Tips

- Manufactured from 400 series stainless steel
- Excellent corrosion resistance
- Sharp tip for precision work around delicate circuits and components
- Double sided with bent flat and curved points
- Eight sided handle is knurled at each end for extra grip



20035

Product ID	Description
20035	Probe Double Sided Scraper Bent Tips

Probe Bent Needle Point

- Manufactured from 400 series stainless steel
- Excellent corrosion resistance
- Sharp tip for precision work around delicate circuits and components
- 90 degree bent point
- Eight sided handle to ensure grip and prevent rolling



20032

Product ID	Description
20032	Probe Bent Needle Point

Probe Double End Bent/Curved

- Manufactured from 400 series stainless steel
- Excellent corrosion resistance
- Sharp tip for precision work around delicate circuits and components
- Double sided with bent and curved points
- Eight sided handle is knurled at each end for extra grip



20039

Product ID	Description
20039	Probe Double End Bent/Curved

Probe Curved Needle Point

- Manufactured from 400 series stainless steel
- Excellent corrosion resistance
- Sharp tip for precision work around delicate circuits and components
- Curved needle point
- Eight sided handle to ensure grip and prevent rolling



20034

Product ID	Description
20034	Probe Curved Needle Point

Stainless Steel Probe 4-Piece Set

- Manufactured from 400 series stainless steel
- Excellent corrosion resistance
- Sharp tip for precision work around delicate circuits and components
- Eight sided handle is knurled at each end for extra grip
- Set of four contains: Straight, Bent, Curved and Angled Models



20210

Product ID	Description
20210	Stainless Steel Probe 4-Piece Set

Did you know Aven offers a **limited lifetime warranty** on all hand tools?
Visit www.AvenTools.com for more information.