

EAN:	4013288221131	Size:	115x60x40 mm
Part number:	05008884001	Weight:	175 g
Article number:	Kraftform Kompakt Stubby Magazin RA 2	Country of origin:	CZ
		Customs tariff number:	82079030

- Short, compact Stubby shape for working in tight installation spaces, with 6 bits in the integrated magazine
- Ergonomic 2-component Kraftform handle for precise work
- Ratchet function with fine toothing for a low return angle and reversible ring (right, fixed, left)
- Captive and swiveling bit magazine for easy removal and safe storage of bits
- Take it easy tool finder: colour coding according to profile and size

Particularly small bitholding screwdriver with extremely short bit mounting for hard to reach areas. With ratchet function and fine toothing for a low return angle. Easy-to-operate reversible ring (right, fixed, left). Includes 6 tough, universal bits, which are located in a magazine in the handle. The strong permanent magnet in the bit mounting ensures secure holding of the bit. The 2-component Kraftform handle with the practical combination of hard and soft zones allows for a firm grip and precise working. Take it easy tool finder: With size stamping and colour coding by output to help you find the required bit easily.

Compact shape



With its compact handle shape and the short blade, the Kraftform Stubbies are particularly suitable for working in confined screwdriving situations.

Handle with integrated bit magazine




The handle can be opened and thus gives access to the six bits contained in the magazine.

Swiveling bit magazine



Captive and swiveling bit magazine for easy removal and safe storage of bits

Ratchet function



The ratchet mechanism is fine-toothed for a low return angle. The screwdriving directions right/fixed/left can be set with the reversible ring. The magnetic bit mounting is suitable for bits with 1/4" external hexagon drive as per DIN ISO 1173-C 6.3 and Wera connection series 1



Web link

https://products.wera.de/en/kraftform_kompakt_kraftform_kompakt_stubby_with_kraftform_bit-holding_stubby_screwdriver_handle_kraftform_kompakt_stubby_magazin_ra_2

Wera - Kraftform Kompakt Stubby Magazin RA 2
05008884001 - 4013288221131


Wera Werkzeuge GmbH
Korzerter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de

BiTorsion Bits

“Take it easy” tool finder



With BiTorsion zone to cushion peak loads.



"Take it easy" tool finder with colour coding according to profiles and size stamp - for simple and rapid accessing of the required tool.

Web link

https://products.wera.de/en/kraftform_kompakt_kraftform_kompakt_stubby_with_kraftform_bit-holding_stubby_screwdriver_handle_kraftform_kompakt_stubby_magazin_ra_2

Wera - Kraftform Kompakt Stubby Magazin RA 2
05008884001 - 4013288221131

Wera Werkzeuge GmbH
Korzerter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de

Kraftform Kompakt Stubby magazine RA 2, 6 pieces

Kraftform Kompakt Stubby - With Kraftform bit-holding Stubby screwdriver handle.



Set contents:

851/1 BTZ bits, PH 1 x 25 mm



05056420001	1x	PH 1 x 25 mm
05056422001	1x	PH 2 x 25 mm

855/1 BTZ bits, PZ 1 x 25 mm



05056720001	1x	PZ 1 x 25 mm
05056722001	1x	PZ 2 x 25 mm

867/1 BTZ TORX® bits, TX 25 x 25 mm



05066126001	1x	TX 25 x 25 mm
-------------	----	---------------

800/1 BTZ bits, 0.8 x 5.5 x 25 mm



05056064001	1x	0.8 x 5.5 x 25 mm
-------------	----	-------------------

Web link

https://products.wera.de/en/kraftform_kompakt_kraftform_kompakt_stubby_with_kraftform_bit-holding_stubby_screwdriver_handle_kraftform_kompakt_stubby_magazin_ra_2

Wera - Kraftform Kompakt Stubby Magazin RA 2
05008884001 - 4013288221131

Wera Werkzeuge GmbH
Korzerter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de