

CHU362DS

Safety switch, heavy duty, non fusible, 60A,
600 VAC/VDC, 3 poles, 60 hp, NEMA 4, 4X, 5,
304 steel



Main

Product	Single Throw Safety Switch
Disconnect Type	Non-fusible disconnect
Number of Poles	3
Electrical Connection	Lugs
Duty Rating	Heavy duty

Complementary

Line Rated Current	60 A
Factory Installed Neutral	None
Mounting Type	Surface
Voltage Rating	600 V AC/DC
Motor power hp	10 Hp at 240 V AC 50-60 Hz for 1 phase motors 20 Hp at 240 V AC 50-60 Hz for 3 phase motors 25 Hp at 480 V AC 50-60 Hz for 1 phase motors 50 Hp at 480 V AC 50-60 Hz for 3 phase motors 30 Hp at 600 V AC 50-60 Hz for 1 phase motors 60 Hp at 600 V AC 50-60 Hz for 3 phase motors 10 Hp at 250 V DC 30 hp at 600 V DC
Wire Size	AWG 14...AWG 3 copper or aluminium
Tightening torque	50 Lbf.In (5.65 N.m) (AWG 3) 45 Lbf.In (5.08 N.m) (AWG 6...AWG 4) 40 Lbf.In (4.52 N.m) 0.01 in ² (8.367 mm ²) (AWG 8) 40 Lbf.In (4.52 N.m) (AWG 8) 50 Lbf.In (5.65 N.m) 0.00...0.01 in ² (2.06...5.261 mm ²) (AWG 14...AWG 10) 50 lbf.in (5.65 N.m) (AWG 14...AWG 10)
Height	16.87 in (428.50 mm)
Width	10.81 in (274.57 mm)
Depth	6.97 in (177.04 mm)

Environment

Certifications	CSA
Enclosure Rating	NEMA 4/4X stainless steel 304

Ordering and shipping details

Category	00153-C,CH&CHU CANADA SW NON-NEG
Discount Schedule	DE1
GTIN	785901994589
Returnability	Yes
Country of origin	US

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	8.70 in (22.098 cm)
Package 1 Width	11.20 in (28.448 cm)
Package 1 Length	19.80 in (50.292 cm)
Package 1 Weight	19.17 lb(US) (8.695 kg)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
PVC free	Yes