



**Part Number :** [08550102](#)  
**Product Description :** KK 254 Crimp Terminal,  
22-30 AWG, Bag, Selective Gold (Au), Nickel  
(Ni) Under Plating  
**Series Number :** 2759  
**Status :** Active  
**Product Category :** Crimp Terminals  
**Engineering Number :** 2759-(555)L  
**Packaging Alternative :** 0008550101 (Reel)



Documents & Resources

Drawings


[Drawing 008550102\\_sd.pdf](#)  
[Packaging Design Drawing PK-2759-001-001.pdf](#)

Specifications

[Product Specification 50510002-PS-000.pdf](#)  
[Product Specification PS-10-07-001.pdf](#)  
[Test Summary TS-10-07-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2023)3788-DC (14 Jun 2023)
EU RoHS	Compliant per EU 2015/863

[Multiple Part Product Compliance Statements](#)

- Eu RoHS
- REACH SVHC
- Low-Halogen

[Multiple Part Industry Compliance Documents](#)

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

## EU RoHS Certificate of Compliance

---

### Part Details

#### General

Status	Active
Category	Crimp Terminals
Series	2759
Description	KK 254 Crimp Terminal, 22-30 AWG, Bag, Selective Gold (Au), Nickel (Ni) Under Plating
Application	Signal, Wire-to-Board
Product Family	KK Interconnect Systems
Product Name	KK 254
UPC	800753745995

#### Physical

Gender	Female
Material - Metal	Brass
Material - Plating Mating	Gold
Material - Plating Termination	Nickel
Net Weight	0.064/g
Packaging Type	Bag
Plating min - Mating	0.381µm
Plating min - Termination	0.762µm
Termination Interface Style	Crimp or Compression
Wire Insulation Diameter	1.57mm max.
Wire Size (AWG)	22, 24, 26, 28, 30
Wire Size mm <sup>2</sup>	N/A

#### Solder Process Data

Lead-Free Process Capability	N/A
------------------------------	-----

---

## Use with Part(s)

Description	Part Number
KK 254 Single Row Crimp Housings	<u>2695</u>
KK 2.50mm Pitch Single Row Receptacle Housings	<u>5051</u>

---

## Application Tooling

### Global

Description	Part Number
Hand Crimp Tool	<u>0011010185</u>
Extraction Tool for KK 2.54mm Terminals, 22-30 AWG	<u>0011030022</u>
PremiumGrade Hand Crimp Tool for KK 2.54mm Crimp Terminals, 22-30 AWG	<u>0638118200</u>
Insertion Tool for KK 2.54mm Terminals, 22-30 AWG	<u>0638120000</u>
Parallel Action Handtool for Terminals, 22-28 AWG Wire	<u>0690080955</u>