

# Miniature Quick Wire Thermocouple Connector Panel Mount with Stainless Steel Bracket IM-K-SSPFQ Type K IEC




Labfacility are the UK's leading manufacturer of Temperature Sensors, Thermocouple Connectors and associated Temperature Instrumentation and stockists of Thermocouple Cables. The Company has been trading since 1971 and is ISO 9001 accredited.

Labfacility have supplied Farnell for over 30 years, and an extensive range of our products are available to buy online, from stock, direct from Farnell.

# **Datasheet**





Miniature Socket 
Quick Wire with stainless steel mounting bracket

(dimensions in mm)

# **Specifications**

General Description	Contacts are polarized to ensure correct connection		
deficial Description	Contacts are polarized to ensure correct connection		
Thermocouple Type	K IEC		
Connector Type	Quick Wire Socket with SS Bracket		
Connector Size	Miniature		
Colour	Green		
Max. Temperature	220°C		
+Positive Contact	Nickel Chromium		
-Negative Contact	Nickel Alloy		
Standards Met	BS EN 50212:1997. RoHS		

# **Ordering Information**

Thermocouple	Colour Code	Size	Style	Manufacturers	Farnell order
Туре				Number	Number
K	IEC	Miniature	Quickwire Stainless	IM-K-SSPFQ	8598304
			Steel Bracket		

CONNECTORS - 42 (K) Dec-23



#### Thermocouple & PRT Cable

Thermocouple cables are available in IEC or ANSI colour codes. Insulation types include PFA, PTFE, PVC &

Fibreglass. Available spool lengths include 10, 25, 50, 100 and 200m.

### Best Sellers



**ANSI PTFE Insulated Twin Twisted** Farnell 2443696 Newark 73AC8304

**ANSI PFA Insulated** Twin Twisted Farnell 2443711 Newark 73AC8297

#### **Fabricated and Specialist Thermocouples**

Styles include; Magnet, Washer, Nozzle, Leaf, Bayonet & Bolt thermocouple. Various lengths and calibration types available.


### **Best Sellers**



Washer Thermocouple Farnell 8597952 Newark 38K1555

**Bayonet** Thermocouple Farnell 2785115 Newark 37AC0993

> Magnet Thermocouple Farnell 2081298 Newark 88T2877



Including exposed junctions with fitted or moulded miniature plug and insulated leads, ideal for test and development applications.

1, 2, 3, 5 & 10m lengths available in IEC or ANSI colours.

# **Best Sellers**



Farnell 2443720 Newark 84X0232

IEC Type T Exposed Junction Farnell 7076186 Newark 68C2613

IEC Type K Exposed Junction Farnell 4100748



#### Thermocouple Connectors

Range of miniature or standard thermocouple connectors. Available in thermocouple types K, J, T, E, N, RS, B, and copper. IEC, ANSI & JIS colour codes available.



#### **IEC Thermocouple PCB Socket** Farnell 2347056 **Newark 06X5514**



**IEC Thermocouple** Plug

Farnell 7086362 **Newark 67C1559** 



ANSI Thermocouple Socket

> Farnell 2347121 Newark 06X4819



#### **RTD Detectors**

Wire-wound type provides greater accuracy and stability but are vulnerable to shock.

Flat film type are resistant to shock and have quicker thermal response times.

Various lengths and diameters available, in class A, B and 1/10th Din.

## **Best Sellers**



PT1000 Thin Film Detector Farnell 8598550 Newark 38K0883

Newark 15J1022

PT100 Wire **Wound Detector** 

Farnell 2770776 Newark 25AC2608

PT100 Class A Thin Film Detector

### Mineral Insulated Thermocouples

Available in various calibration types with a variety of terminations.

These include; Thermocouple plugs, Terminal heads and Thermocouple cable.





**ANSI Thermocouple** Farnell 2420317 Newark 53X3217

IEC Thermocouple with Mini Plug Farnell 4248338

**Newark 19J1166** 

Newark 44AC8638

**IEC Melt Bolt** Thermocouple Farnell 2816490







Detectors (RTD) / Platinum Resistance Thermometers (PRT)

To suit a wide range of applications and styles, available in class A or B.

Sensor Probe Farnell 8598096 Newark 38K0974

Pt100 Sensor in Stainless Steel Tube with Teflon Lead Farnell 2420300 Newark 53X3459

Pt100 Outdoor/ Cold Store Temperature Sensor Farnell 2816462

Newark 44AC8648



# Thermocouple Welder

The Thermocouple Welder is a compact, simple-to-use instrument designed for thermocouple and fine wire welding. Supplied with foot switch, spare electrodes, pliers & safety glasses, impact clip and pen plate.

### **Best Sellers**





L60+ Thermocouple & Fine Wire Welder and accessories Farnell 2897470 Newark 62AC8741

CONNECTORS - 42 (K)

Dec-23