

## 5.25in Trayless Hot Swap Mobile Rack for 3.5in Hard Drive

**Product ID:** HSB100SATBK



This 3.5in SATA hard drive hot-swap bay allows you to install a 3.5in SATA drive in an available/unused 5.25in drive bay. To remove the drive, it's as simple as opening the front panel door; to re-insert a drive, simply insert the drive (connector first) until the door closes.

The hot swap bay offers a trayless design that makes it the ideal solution for quick and easy drive removals and insertions as part of a system building process, or integration into rackmount systems or industrial environments.

To maximize performance and utilize the full speed potential of your SATA III hard drives, this HDD Backplane supports SATA III for transfer speeds up to 6 Gbps when paired with a compatible controller.

Also a perfect addition for operating system image deployment and any task that requires being able to quickly access large volumes of data on the fly, the hot swap bay provides everything you need to expedite important projects while maintaining a reliable storage solution.

With support for SATA HDD speeds up to 6.0 Gbps, the mobile rack/backplane is fully compatible with RAID installations to ensure maximum performance and versatility for enhanced storage applications.

Designed to provide a durable and reliable operating experience, the mobile rack features a 50,000+ insertion rating and is backed by StarTech.com's 2-year warranty.

### Certifications, Reports and Compatibility





## Applications

- Add additional hot-swap bays to a server or workstation computer
- Replace or upgrade old IDE backplane with a SATA backplane
- System builders who need to image drives quickly and efficiently
- Environments where drives need to be replaced/removed regularly, without external protection for the drives required after removal
- Be able to replace/remove individual drives from a storage array with minimal or no system down time

## Features

- Holds a 3.5" SATA drive in a front accessible 5.25" bay
- Trayless design: drives are not mounted into separate trays/enclosures
- Lockable drive bay
- Internal rubber shock absorbers
- 50,000+ insertion rating
- Power and Activity LED indicator
- Support for SATA revision I/II/III (1.5/3.0/6.0 Gbps)
- Supports 3.5" form factor SATA hard drives
- Plug-and-Play and Hot-Swap compatible

---

### Hardware

Warranty	2 Years
Front Door Key Lock	Yes
Number of Drives	1
Drive Size	3.5in
Compatible Drive Types	SATA

---

**Performance**

Hot Swap Capability	Yes
Insertion Rating	50,000+ Cycles
Temperature Alarm	No

---

**Connector(s)**

Drive Connectors	1 - SATA (7 pin, Data)
	1 - SATA Power (15 pin)
Host Connectors	1 - SATA Power (15 pin)
	1 - SATA (7 pin, Data)

---

**Software**

OS Compatibility	OS independent; No software or drivers required
------------------	-------------------------------------------------

---

**Indicators**

LED Indicators	1 - Drive Power/Activity
----------------	--------------------------

---

**Environmental**

Operating Temperature	0C to 50C (32F to 122F)
Humidity	Operating - 5~85% RH Non-condensing
	Storage - 5~95%

---

**Physical Characteristics**

Color	Black
Material	Aluminum and Plastic
Product Length	7.2 in [18.4 cm]
Product Width	5.9 in [14.9 cm]
Product Height	1.7 in [4.2 cm]
Weight of Product	9.2 oz [261.0 g]

---

**Packaging Information**

Package Quantity	1
Package Length	6.3 in [15.9 cm]

Package Width	8.1 in [20.6 cm]
Package Height	2.0 in [51.0 mm]
Shipping (Package) Weight	12.9 oz [366.0 g]

---

**What's in the Box**

Included in Package	1 - 5.25" Tray-Less SATA Hot-Swap Bay
	2 - Key
	1 - Screw Kit
	1 - Instruction Manual
	1 - Drive Activity LED and 2 Pin Wire

---

***\*Product appearance and specifications are subject to change without notice.***