



Part Number : [2209570108](#)

Product Description : T1 Industrial Single-Pair Ethernet (SPE) Plug Cable Assembly, IP20, 5.0m Cable Length

Series Number : 220957

Status : Active

Product Category : I/O Cable Assemblies



---

## Documents & Resources

### Drawings

[Drawing 2209570108\\_sd.pdf](#)

---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Reviewed per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2023)3788-DC (14 Jun 2023)
EU RoHS	Not Reviewed per EU 2015/863

### Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

### Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

### EU RoHS Certificate of Compliance

---

## Part Details

## General

Status	Active
Category	I/O Cable Assemblies
Series	220957
Description	T1 Industrial Single-Pair Ethernet (SPE) Plug Cable Assembly, IP20, 5.0m Cable Length
Assembly Configuration	Dual Ended Connectors
Connector to Connector	SPE-to-SPE
Product Family	T1 Industrial Single-Pair Ethernet (SPE) Connectors and Cable Assemblies
Product Name	Single-Pair Ethernet (SPE)
UPC	196823192364

## Electrical

Current - Maximum per Contact	4.0A
Data Rate	Up to 1.0 Gbps
Shielded	Yes
Voltage - Maximum	60V AC

## Physical

Cable Length	5.0m
Circuits (Loaded)	2
Circuits (maximum)	2
Gender	Plug/Plug
Lock to Mating Part	Yes
Material - Metal	Copper
Material - Plating Mating	Gold
Net Weight	167.860/g
Packaging Type	Bag
Single Ended	No
Waterproof / Dustproof	Yes
Waterproof / Dustproof Type	IP20
Wire/Cable Type	PUR, Twisted Pair
Wire Size (AWG)	1 x 2 x AWG 26/19

---

## Mates With / Use With

### Mates with Part(s)

Description	Part Number
T1 Industrial Single-Pair Ethernet (SPE) PCB Jack, Right-Angle, IP20	<u>2209570001</u>

---

This document was generated on Dec 24, 2023