

USB-C™ Pro Multiport Hub 8 Port CMH-08



USB-C Port for
Power Charging



2x 4K HDMI
Video Connection



3x Data Ports
USB-A 3.2 Gen1



SD/microSD Slot

No more limits for your laptop

Introducing the USB-C Pro Multiport Hub 8 Port CMH-08, a connectivity powerhouse for streamlined productivity. Unleash enhanced connectivity by converting a single USB-C port into eight versatile ports, including USB 3.2 and HDMI.

Swift data transfer is at your fingertips with USB 3.2 Gen 1 technology, ensuring efficient workflows and minimal wait times. Immerse yourself in crisp 4K video output through the HDMI port, ideal for presentations, movie watching, or expanding your workspace with crystal-clear visuals. Do you need a card reader too? Well this Hub comes with card reader slots for both SD and microSD memory cards.


Plug the Hub into the USB-C™ port on your laptop to immediately increase your working possibilities.

USB-C™ Pro Multiport Hub

8 Port

CMH-08

General Information	
Material	Aluminum+ABS
Colour	Silver
Interfaces	
Host Connection	USB-C™ 3.1 Gen2 with up to 85W power pass-through
Cable length	15 cm
Video Ports	HDMI 1: up to 8K@30Hz (7680x4320) (works separately if source DP 1.4) / up to 4K@60Hz (3840x2160) (works separately if source DP 1.2) HDMI 2: up to 4K@30Hz (3840x2160) (works separately if source DP 1.2)
SD/microSD Slot	Read: up to 104MB/s, Write: up to 80MB/s (Data transfer rate are subject to the speed of the memory card itself and your computer's USB ports)
USB-A ports	3x USB-A 3.2 Gen1, 5Gb/s data speed, downwards compatible with USB 2.0, Max. power output 5V 0.9A@4.5W
USB-C ports	1x USB-C 3.2 Gen1, 5Gb/s data transmission compatible with PD (Power Delivery), Input Power: up to 100W (15W is reserved for other ports)
Other Features	
Certificates	EAC/CE/UKCA/FCC
ROHS/REACH compliance	Yes
Storage and Operating Conditions	
Operating Temperature	0°C ~ +40°C
Storage Temperature	-20°C ~ +70°C
Operating Humidity	10% ~ 85% RH (no condensation)



USB-C™ Pro Multiport Hub 8 Port

CMH-08



PN	Description	Bar Code	EAN128 Code	EAN14 Code
32151	USB-C Pro Multiport Hub 8 Port CMH-08	023942321514	(02)00023942321514(37)10(91)891 (02)00023942321514(37)40(91)891	20023942321518 50023942321519

Logistic Information	
Product Dimensions L x W x H	121 x 40 x 13mm
Product Weight	79 grams
Units per Pack	1
Pack Dimensions L x W x H	155 x 85 x 20mm
Pack Weight	123
Units per Inner Carton	10
Inner Carton Dimensions L x W x H	325 x 97 x 110mm
Inner Carton Weight	1 340
Units per Outer Carton	40
Outer Carton Dimensions L x W x H	345 x 215 x 250mm
Master Cartons Weight	5 760
Master Cartons per Layer	12
Layers per Pallet	4
Units per Pallet	1 920

USB-C™ Pro Multiport Hub 8 Port

CMH-08



Front Angled



Back Angled



Left Side Angled



Right Side Angled



Top Angled



Ports



Right Side Angled Lit



Packaging 3D



Packaging flat



Lifestyle 1



Lifestyle 2



Lifestyle 3

System Requirements:

- Interface: USB-C must support video output.
- OS: Windows OS 7/8/10/11 (X86/X64), Mac OS 10.2 Above, Chrome OS, Linux, Android 7 or above

Pack Contents:

- USB-C Pro Multiport Hub
- Quick Start Guide