

# Product data sheet

Specifications

**SQUARE D**

**Green Premium™**



## Circuit breaker enclosure, LA, LH, Q4, 125A to 400A, NEMA 1, 15.28in W x 44.48in H x 6.5in D

LA400S

**Product availability : Stock - Normally stocked in distribution facility**

### Main

**Breaker Compatibility** Circuit breaker LAL/LHL/Q4L/KAL/KHL 125...400 A

### Complementary

**Height** 44.48 in (1129.79 mm)

**Width** 15.28 in (388.11 mm)

**Depth** 6.50 in (165.10 mm)

### Environmental

**NEMA Degree of Protection** NEMA 1

### Ordering and shipping details

**Category** 00030-IND CB ENCL NEMA 1,3R

**Discount Schedule** DE1

**GTIN** 785901508014

**Returnability** Yes

**Country of origin** MX

### Packing Units

**Unit Type of Package 1** PCE

**Number of Units in Package 1** 1

**Package 1 Height** 7.60 in (19.3 cm)

**Package 1 Width** 15.91 in (40.4 cm)

**Package 1 Length** 44.80 in (113.8 cm)

**Package 1 Weight** 53.99 lb(US) (24.49 kg)

**Unit Type of Package 2** PAL

**Number of Units in Package 2** 8

**Package 2 Height** 40.00 in (101.6 cm)

**Package 2 Width** 40.00 in (101.6 cm)

**Package 2 Length** 48.00 in (121.92 cm)

---

**Package 2 Weight** 431.93 lb(US) (195.92 kg)

## Offer Sustainability

---

**Sustainable offer status** Green Premium product

---

**California proposition 65** WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to [www.P65Warnings.ca.gov](http://www.P65Warnings.ca.gov)

---

**REACH Regulation** [REACH Declaration](#)

---

**EU RoHS Directive** Compliant  
[EU RoHS Declaration](#)

---

**Toxic heavy metal free** Yes

---

**Mercury free** Yes

---

**RoHS exemption information** [Yes](#)

---

**China RoHS Regulation** [China RoHS declaration](#)  
Pro-active China RoHS declaration (out of China RoHS legal scope)

---

**Environmental Disclosure** [Product Environmental Profile](#)

---

**PVC free** Yes

---

**Halogen content performance** Halogen free plastic parts product

---

## Contractual warranty

---

**Warranty** 18 months

**Recommended replacement(s)**