

High

Weatherproof Padlocks

With 180 years of manufacturing expertise, an exclusive Yale design and rigorous testing, the Yale Weatherproof Padlocks have been built with you in mind. Suitable for a garden shed, gate, or any other outdoor high value items you want to keep safe and secure. Our padlocks come in 3 different sizes, with hardened steel shackle to prevent cutting and protective cover on the body and shackle for additional weatherproof protection. Yale takes care of your possessions; you take care of the rest.



Suitable for



Outdoors



Sheds



Gates

Features

- Hardened steel shackles to prevent cutting.
- Protective cover on the body and shackle plus key hole cover for additional weatherproof protection.
- Double ball locking for added security.
- Multi packs available in 35mm and 51mm Weatherproof Padlock with keyed alike for convenience.
- Tested to EN12320:2012 for different forms of attack such as cutting, pulling and twisting of the shackle.
- Tested up to 120 hours for corrosion resistance to ensure protection against weather conditions.
- Tested to 10,000 cycles (opening and closing) for optimum performance.
- 10% footprint reduction on Yale padlock packaging.



Y220B/51/118/1



Y222B/35/122/3



Y221B/52/125/1



Y220B/61/123/1



Y220B/71/130/1

High



Weatherproof Padlocks



Description	Weatherproof Padlock 35mm keyed alike pk3	Weatherproof Padlock 51mm	Weatherproof Padlock Closed Shackle 51mm	Weatherproof Padlock 61mm	Weatherproof Padlock 71mm
Part no.	Y222B/35/122/3	Y220B/51/118/1	Y221B/52/125/1	Y220B/61/123/1	Y220B/71/130/1
Locking points	Single locking Brass latch	Double locking stainless steel ball	Double locking stainless steel ball	Double locking stainless steel ball	Double locking stainless steel ball
Body material	Laminated steel	Laminated steel	Laminated steel	Laminated steel	Laminated steel
Shackle material	Hardened steel	Hardened steel	Hardened steel	Hardened steel	Hardened steel
Vertical shackle clearance	24mm	24mm	22mm	27mm	29mm
Horizontal shackle clearance	12mm	18mm	18mm	21mm	26mm
Weight with keys (grams)	335g	300g	515g	455g	700g
Dimensions (mm)	Body W: 40 Body H: 37.8 Body D: 26 Shackle Ø: 5	Body W: 53 Body H: 50 Body D: 35 Shackle Ø: 9	Body W: 53 Body H: 82 Body D: 35 Shackle Ø: 9	Body W: 62 Body H: 55 Body D: 38 Shackle Ø: 12	Body W: 72 Body H: 60 Body D: 43 Shackle Ø: 13
Corrosion resistance	120 hours	120 hours	120 hours	120 hours	120 hours
Keys	3 keys	3 keys	3 keys	3 keys	3 keys
Pins	5 pin cylinder	5 pin cylinder	5 pin cylinder	5 pin cylinder	5 pin cylinder
CEN rating	-	2	2	2	3

For more information on our products, please visit:

www.yalelock.com



Yale EMEA
School Street, Willenhall,
West Midlands WV13 3PW