Product data sheet

Specifications



Harmony XBT - direct connection cable - for XBTGK, XBTGT, XBTGR - 2.5 m

XBTZG9721

Product availability : Stock - Normally stocked in distribution facility

Main

Range of Product	Harmony XBT
Accessory / separate part category	Connection accessories
Accessory / Separate Part Type	Connecting cable
Accessory / separate part designation	Direct connection cable
Accessory / separate part destination	Direct connection of XBT terminal to Siemens Simatic PLC Small touch screen panel

Complementary

Product Compatibility	XBTGT6... XBTGT5... XBTRT500 XBTRT511 XBTGK.... XBTGT4... XBTGT1... XBTGT7340 XBTGT2...
Range Compatibility	Harmony HMI GTO Siemens S7-400 Siemens S7-200 Siemens S7-300 Harmony STO & STU
Cable length	8.20 ft (2.5 m)
Electrical connection	1 male connector RJ45 1 male connector SUB-D 9
Communication port protocol	PPI MPI
Physical interface	RS485

Ordering and shipping details

Category	22569-MAGELIS XBT-GT (AND XBT-G)
Discount Schedule	MC2
GTIN	3595863885538
Returnability	No
Country of origin	CN

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	0.59 in (1.5 cm)
Package 1 Width	5.51 in (14 cm)
Package 1 Length	5.91 in (15 cm)
Package 1 Weight	4.09 oz (116 g)
Unit Type of Package 2	S03
Number of Units in Package 2	60
Package 2 Height	11.81 in (30 cm)
Package 2 Width	11.81 in (30 cm)
Package 2 Length	15.75 in (40 cm)
Package 2 Weight	15.34 lb(US) (6.96 kg)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACh Regulation	REACh Declaration
REACh free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
China RoHS Regulation	China RoHS declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Contractual warranty

Warranty	18 months

Recommended replacement(s)