

Please note that the data given here has been taken from the online catalog. For comprehensive information and data, please refer to the user documentation at <http://www.download.phoenixcontact.com>. The General Terms and Conditions of Use apply to Internet downloads.

## ▶ Extract from the online catalog



Electronic housing, for PCB insertion, fully equipped with 3 screw or 6 tab connections per side

Illustration shows version UEGM 22.5

Order No.	2792015
Ord designation	UEGM 25
EAN	4017918072520
Pack	10 Pcs.
Customs tariff	85369010
Weight/Piece	0,05804 KG
Catalog page information	Page 366 (CC-2005)

## ▶ Product notes

WEEE/RoHS-compliant since: 01/01/2003



**IMPORTANT :** This date is valid for Customers in Germany only. Date Format is MM/DD/YYYY. Please contact your local in-country Phoenix Contact location or designated business partner for a Logistics Compliant date in your area. In order to guarantee delivery of RoHS-Compliant product, please purchase Phoenix Contact parts from authorized Phoenix Contact representatives and distributors.

## ► Certificates / Approvals

---

### Certificate logos



#### **CUL**

Nominal voltage $U_N$	300 V
Nominal current $I_N$	10 A
AWG/kcmil	30-12

---


#### **UL**

Nominal voltage $U_N$	300 V
Nominal current $I_N$	10 A
AWG/kcmil	30-12



---

## ► Drawings

### Explosion drawing




### Dimensioned drawing



UEGM 25... und UEGM 27,5-SMD with 1 PCB,  
6 positions or 12 positions (FS/FS)

Schematic diagram



## ► Accessories

Item	Designation	Description
<b>Bridges</b>		
2820916	DB 50- 90 BK	Wire bridge, 50-position, divisible, for bridging identical inputs and outputs, 0.5 mm <sup>2</sup> , insulation: black
2820929	DB 50- 90 GY	Wire bridge, 50-position, divisible, for bridging identical inputs and outputs, 0.5 mm <sup>2</sup> , insulation: gray
<b>Cable/conductor</b>		
1406700	PT/FS 2,8	Plastic sheath, as touch protection, slide onto the conductor before for 2.8 slip-on sleeves
0604707	PT/FS 6,3	Plastic sheath, as touch protection, slide onto the conductor before for 6.3 slip-on sleeves
<b>General</b>		
2792109	P 1-UEGM	PCB, for screw and slip-on connection, for custom fitting electronic components.
<b>Marking</b>		
1050004	ZB 5 :UNBEDRUCKT	Zack strip, unprinted, 10-section, for individual labeling with M-PEN, ZB-T or CMS system, pack is sufficient for 100 terminal blocks, for a terminal width of 5.2 mm, color: White
<b>Plug/Adapter</b>		
2790389	UEG-MT-FS	Metal part for slip-on connection, to increase the number of positions.

---

## ► Address

---

PHOENIX CONTACT GmbH & Co. KG  
Flachsmarktstr. 8  
32825 Blomberg  
Germany  
Phone +49 5235 3 00  
Fax +49 5235 3 41200  
<http://www.phoenixcontact.com>  
Phoenix Contact  
Technical modifications reserved;