

# Category 5e Enhanced Patch Cords

**multicomp** PRO

**RoHS  
Compliant**



## Description

Snagless, Booted Category 5e Utp Patch Cords


## Features

- Snagless boots to prevent cable kinks and bent pins when removing from patch panels.

## Specifications:

- Booted (snagless) and nonbooted versions — in 8 lengths and 7 popular colors
- 8-position RJ-45 module plug at each end — 15 $\mu$ " gold-plated copper alloy contacts
- Category 5e LAN cable — 4 unshielded twisted pairs (UTP), 24 AWG, PVC jacket
- Cable speeds up to 350MHz
- Verified to ANSI/TIA-568-C.2

## Diagram



No.	Item	Q'ty.	Description
1	Enhance Category 5e UTP Lan Cable	1Pc	#24 × 4P+Jacket : PVC, O.D.: 5.2mm Frequency : 350MHz
2	RJ-45 8P8C Modular Plug	2 Set	Contact : Copper Alloy 15 $\mu$ ", Gold Plated Insulator : Polycarbonate Colour : Natural
3	PVC Boot	2 Pcs	PVC, Shore A : 75 $\pm$ 3

**multicomp** PRO

# Category 5e Enhanced Patch Cords

Wire Connection Table			
8	Brown	Twisted Pair	8
7	White/Brown		7
5	White/Blue	Twisted Pair	5
4	Blue		4
6	Green	Twisted Pair	6
3	White/Green		3
2	Orange	Twisted Pair	2
1	White/Orange		1
J1	Wire Colour		J2

## Part Number Table

Description	Length (Feet)	Colour	Part Number
Cat. 5e Patch Cords, W / SR	1 ±0.5"	Black	SPC21956
		Black	SPC21957
		Green	SPC21958
		White	SPC21959
	3 ±1"	Red	SPC21962
		Green	SPC21993
		Yellow	SPC21963
		White	SPC21901
		Black	SPC21960
		Blue	SPC21961
	4 ±1"	Blue	SPC20043
	5 ±1"	Black	SPC21900
		Blue	SPC21899
		Green	SPC21994
		Red	SPC21995
		Yellow	SPC21996
		White	SPC21997
	7 ±1"	Green	SPC21966
		Red	SPC21967
		Black	SPC21964
		Yellow	SPC21968
		White	SPC21969
		Blue	SPC22013

# Category 5e Enhanced Patch Cords

**multicomp** PRO

Description	Length (Feet)	Colour	Part Number
Cat. 5e Patch Cords, W / SR	10 ±1.5"	Black	SPC21970
		Blue	SPC21971
		Green	SPC21972
		Yellow	SPC21974
		White	SPC21975
		Red	SPC21973
	15 ±1.5"	Black	SPC21976
		Green	SPC21978
		Red	SPC21979
	25 ±2"	Black	SPC21982
		Blue	SPC21983
		Green	SPC21984
		Yellow	SPC21986
		White	SPC21987
		Red	SPC21985
	50 ±4"	Black	SPC21988
		Blue	SPC21989
		Green	SPC21990
		Yellow	SPC21991
White		SPC21992	

**Important Notice :** This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro  
Farnell.com/multicomp-pro  
sg.element14.com/b/multicomp-pro

**multicomp** PRO