

Product data sheet

Specifications



fuse cartridge 5 x 20 - fast blow 2 A - without indication

ABE7FU200

Product availability : Stock - Normally stocked in distribution facility

Main

| | |
|---------------------------------------|---------------------|
| Range of Product | Modicon ABE7 |
| Accessory / separate part designation | Fast blow fuse |
| Accessory / Separate Part Type | Fast blow fuse |
| Accessory / separate part category | Fuses |
| Accessory / separate part destination | Connection sub-base |
| Quantity per Set | Set of 10 |

Complementary

| | |
|--------------------------------|-----------------------|
| Line Rated Current | 2 A |
| Fuse size | 5 x 20 mm |
| Fuse curve | Fast blow |
| Local signalling | Without |
| [Ue] rated operational voltage | 250 V |
| Net Weight | 0.02 lb(US) (0.01 kg) |

Environment

| | |
|------------------------|----|
| Product Certifications | UL |
|------------------------|----|

Ordering and shipping details

| | |
|-------------------|---------------------------------|
| Category | 22375-INTERFACE MODULE(ABA,R,S) |
| Discount Schedule | CP2 |
| GTIN | 3389110602845 |
| Returnability | No |
| Country of origin | LV |

Packing Units

| | |
|------------------------|-----|
| Unit Type of Package 1 | PCE |
|------------------------|-----|

| | |
|-------------------------------------|------------------|
| Number of Units in Package 1 | 1 |
| Package 1 Height | 0.39 in (1 cm) |
| Package 1 Width | 0.98 in (2.5 cm) |
| Package 1 Length | 2.36 in (6 cm) |
| Package 1 Weight | 0.04 oz (1 g) |
| Unit Type of Package 2 | BB1 |
| Number of Units in Package 2 | 10 |
| Package 2 Height | 0.39 in (1 cm) |
| Package 2 Width | 0.98 in (2.5 cm) |
| Package 2 Length | 2.36 in (6 cm) |
| Package 2 Weight | 0.39 oz (11 g) |
| Unit Type of Package 3 | S01 |
| Number of Units in Package 3 | 100 |
| Package 3 Height | 5.91 in (15 cm) |
| Package 3 Width | 5.91 in (15 cm) |
| Package 3 Length | 15.75 in (40 cm) |
| Package 3 Weight | 10.37 oz (294 g) |

Offer Sustainability

| | |
|-----------------------------------|---|
| California proposition 65 | WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov |
| REACH Regulation | REACH Declaration |
| REACH free of SVHC | Yes |
| EU RoHS Directive | Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration |
| Toxic heavy metal free | Yes |
| Mercury free | Yes |
| China RoHS Regulation | China RoHS declaration |
| RoHS exemption information | Yes |

Contractual warranty

| | |
|-----------------|-----------|
| Warranty | 18 months |
|-----------------|-----------|

Recommended replacement(s)