



CorePro Plastic LED Specialities



Corepro LED T25 ND 1.7-15W E14 827

The LED specialities can be easily intalled for certain applications.

Product data

General Information	
Cap base	E14
Nominal lifetime	15,000 h
Switching Cycle	50,000
Lighting Technology	LED
EU RoHS compliant	Yes

Light Technical	
Colour Code	827 [CCT of 2700K]
Beam angle (nom.)	240 degree(s)
Luminous Flux	150 lm
Colour designation	Warm White (WW)
Correlated Colour Temperature	2700 K
Luminous efficacy (rated) (nom.)	88.00 lm/W
Colour consistency	<6
Colour rendering index (CRI)	80
LLMF at end of nominal lifetime (nom.)	70 %
Flickering value (PstLM)	1
Stroboscopic effect	0.4
Photobiological safety according to EN 62471	RG0

Operating and Electrical	
Line Frequency	50 to 60 Hz

Input frequency	50 to 60 Hz
Power Consumption	1.7 W
Lamp current (nom.)	20 mA
Wattage equivalent	15 W
Starting time (nom.)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.4
Voltage (nom.)	220-240 V

Temperature	
T-Case maximum (nom.)	55 °C

Controls and Dimming	
Dimmable	No

Mechanical and Housing	
Lamp Finish	Frosted
Bulb shape	T25


Approval and Application	
Energy Efficiency Class	F
Energy consumption kWh/1,000 hours	2 kWh
EPREL registration number	391879

CorePro Plastic LED Specialities

EyeComfort	Yes
Application Conditions	
Can it be used in closed luminaires	No
Product Data	
Order product name	Corepro LED T25 ND 1.7-15W E14 827
Full product name	Corepro LED T25 ND 1.7-15W E14 827
Full EOC	871951438986100



Order code	38986100
Material no. (12 NC)	929001325702
SAP numerator – quantity per pack	1
EAN/UPC – Product/Case	8719514389861
Numerator – packs per outer box	12
EAN/UPC - Case	8719514389878

Dimensional drawing




Product	D	C
Corepro LED T25 ND 1.7-15W E14 827	25 mm	59 mm

Photometric data



Light Distribution Diagram - Corepro LED T25 ND 1.7-15W E14 827

General uniform lighting - Corepro LED T25 ND 1.7-15W E14 827



Spectral Power Distribution Colour - Corepro LED T25 ND 1.7-15W E14 827

Lifetime



Life Expectancy Diagram - Corepro LED T25 ND 1.7-15W E14 827



Lumen Maintenance Diagram - Corepro LED T25 ND 1.7-15W E14 827

