

Router Trimmer LXT®

DRT50ZX4

18V • 6/8 mm

Light brushless manual trimmer with a wide range of accessories for carpentry

Handy trimmer for carpentry or hobbies. With the router trimmer, you can cut grooves or decorative trimmings in wood. Comes with 6 and 8 mm collets, guide rule, dust extraction adapter and edge milling and router modules. Wide range of blades. Equipped with an LED light.



Technical specifications

Vibration Level, Cutting Grooves in MDF	4,5 m/s ²
Vibration Level, Rotation Without Load	≤ 2,5 m/s ²
Vibration Uncertainty (K Factor), Cutting Grooves in MDF	1,5 m/s ²
Vibration Uncertainty (K Factor), Rotation Without Load	1,5 m/s ²
Voltage LXT	✓
Nominal Battery Voltage	18 V
Battery Chemistry (Ni-Cd / Ni-MH / Li-ion)	Li-ion
Max Output Power	800 W
No load speed	10000 - 30000 min ⁻¹
Max. Collet Capacity	0 - 1-3/8 "
Plunge capacity	0 - 40 mm
Plunge capacity with trimmer base	0 - 40 mm
Plunge capacity with plunge base	0 - 35 mm
Max. Collet Capacity	6 / 8 mm

User benefits

- Brushless maintenance-free and long-life motor
- Battery protection system automatically shuts off power when the battery level is low

EAN 0088381846172

Link to product - www.makitauk.com



Related products

Standard AC

122703-7
Trimmer Guide Assembly



122965-7
Straight guide assembly



195559-1
Dust Nozzle



Optional AC

122391-0
Straight Guide



122703-7
Trimmer Guide Assembly



122965-7
Straight guide assembly



153489-2
Grip complete 125 mm



162258-0
Side Handle



164834-6
Straight Guide



193312-9
Micro Adjustable Straight Guide



194367-7
Guide rail, 3 000 mm



194385-5
Clamp set



194579-2
Guide rail adapter



194733-8
Dust nozzle set Ø 32 / 37 mm



195559-1
Dust Nozzle



195562-2
Offset base set



195563-0
Plunge base set



195564-8
Guide Holder Set



198885-7
Guide rail joint connector set, 2 pcs



198987-9
Router Tilt Base



199140-0
Guide rail, 1 000 mm



199826-6
Quick-Release Ratcheting Guide Rail



343577-5
Templet Guide 8 x 10 x 9,5 mm



344364-5
Templet Guide 14,5 x 16 x 13 mm



763618-5
Collet cone 8 mm



763619-3
Collet Cone 3/8"



763636-3
Collet cone 6 mm



781011-1
Wrench 22 mm



781039-9
Wrench 13



821552-6
Makpac case (4)



837247-1
MakPac (4) Inlay



Optional AC

B-57613

Guide rail bag



P-20177

Guide Rail Connector Set



Other

User manual

Parts drawing