


Kraftform Kompakt VDE



EAN:	4013288229953	Size:	230x120x82 mm
Part number:	05006609001	Weight:	845 g
Article number:	Kraftform Kompakt VDE 16 Torque 1,2-3,0 Nm extra slim 1 Tool Finder	Country of origin:	CZ
		Customs tariff number:	82054000

- Kraftform Kompakt VDE torque screwdriver set with adjustable torque
- Adjustable Kraftform VDE torque holder exclusively for Wera VDE interchangeable blades
- VDE-insulated Kraftform 817 VDE bitholding screwdriver with anti-roll protection
- VDE blades (157 mm length) with practical spinning function, anti-roll protection and "Take it easy" Tool finder: Colour coding by profile and laser-engraved size indication
- Individually tested tools as per IEC 60900
- In robust pouch
- Suitable for Wera 2go

16-piece torque VDE blade set. Includes 14 blades (12 of which with reduced blade diameter) with integrated protective insulation. With "Take it easy" Tool finder: Colour coding by profile and laser-engraved size indication - for quick and easy identification of the required tool. Torque VDE bitholding screwdriver with adjustable torque value from 1.2-3.0 Nm and 817 VDE bitholding screwdriver. Both with ergonomic Kraftform Plus handle, with hard handle zones ensuring high working speeds while soft handle zones guarantee a high torque transfer.



Web link

https://products.wera.de/en/tools_for_electricians_kraftform_kompakt_vde_kraftform_kompakt_vde_16_torque_1_2-3_0_nm_extra_slim_1_tool_finder.html

Wera - Kraftform Kompakt VDE 16 Torque 1,2-3,0 Nm extra slim 1 Tool Finder
05006609001 - 4013288229953

Wera Werkzeuge GmbH
Korzerter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de

Kraftform Kompakt VDE

Individually tested



Each Kraftform Kompakt VDE set has been tested individually at 10,000 volts, in accordance with IEC 60900. This ten-times-higher testing load guarantees safe working at their maximum permitted load of 1,000 volts.

Handle/interchangeable blade system – Kraftform Kompakt VDE



The handle/interchangeable blade system allows rapid exchange of the blades required for a wide range of applications.

Kraftform adjustable torque handle for Electricians




Easy-to-read scale value. Measurement accuracy is $\pm 6\%$ in accordance with the standard EN ISO 6789.

PlusMinus screwdrivers




For the use in terminal blocks, control cabinets, switches, relays, sockets etc.

VDE interchangeable blade with reduced shaft diameter




Reduced blade diameter with integrated protective insulation, allows sunken screws and spring elements to be accessed and actuated, individually tested as per IEC 60900.

“Take it easy”




The Kraftform Kompakt VDE blades are equipped with the “Take it easy” Tool finder. The colour coding by profile and the laser-engraved size indication make it easy to identify the required tool quickly.

Hexagonal anti-roll feature against rolling away



The Kraftform Kompakt blades come with an anti-roll protection. The hexagonal shape hinders the blade from rolling away annoyingly at the workplace.

Fast spinning



The palm of your hand is comfortably supported on the rounded shape of the rear end of the blades. This allows quick spinning of the blade and accelerates the screwdriving process.

Web link

https://products.wera.de/en/tools_for_electricians_kraftform_kompakt_vde_kraftform_kompakt_vde_16_torque_1_2-3_0_nm_extra_slim_1_tool_finder.html

Wera - Kraftform Kompakt VDE 16 Torque 1,2-3,0 Nm extra slim 1 Tool Finder
05006609001 - 4013288229953

Wera Werkzeuge GmbH
Korzerter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de

Kraftform Kompakt VDE 16 Torque 1.2-3.0 Nm extra slim 1 Tool finder, 16 pieces



Kraftform Kompakt VDE

Set contents:

Series 7400 VDE Kraftform adjustable torque handle (0.3-3.5 Nm), 7441 VDE x 1.2-3.0 Nm



05074750001

1x 7441 VDE x 1.2-3.0 Nm



817 VDE Kraftform blade-holding handle, 9 x 98 mm



05003990001

1x 9 x 98 mm



Kraftform Kompakt VDE 62 iS Take it easy, PH 1 x 157 mm



05006512001

1x PH 1 x 157 mm

05006513001

1x PH 2 x 157 mm



Kraftform Kompakt VDE 65 iS Take it easy, PZ 1 x 157 mm



05006526001

1x PZ 1 x 157 mm

05006527001

1x PZ 2 x 157 mm



Kraftform Kompakt VDE 65 iS PZ/S Take it easy, # 1 x 157 mm



05006530001

1x # 1 x 157 mm

05006531001

1x # 2 x 157 mm



Kraftform Kompakt VDE 67 i TORX® Take it easy, TX 10 x 157 mm



05006534001

1x TX 10 x 157 mm



Kraftform Kompakt VDE 67 iS TORX® Take it easy, TX 15 x 157 mm



05006540001

1x TX 15 x 157 mm

05006541001

1x TX 20 x 157 mm

05006542001

1x TX 25 x 157 mm



Kraftform Kompakt VDE 60 i Take it easy, 0.4 x 2.5 x 157 mm



05006500001

1x 0.4 x 2.5 x 157 mm



Kraftform Kompakt VDE 60 iS Take it easy, 0.6 x 3.5 x 157 mm



05006506001

1x 0.6 x 3.5 x 157 mm

05006507001

1x 0.8 x 4 x 157 mm

05006508001

1x 1 x 5.5 x 157 mm



Hook and Loop Fastener Strip 70, 50 x 70 mm

1x 50 x 70 mm



Web link

https://products.wera.de/en/tools_for_electricians_kraftform_kompakt_vde_kraftform_kompakt_vde_16_torque_1_2-3_0_nm_extra_slim_1_tool_finder.html

Wera - Kraftform Kompakt VDE 16 Torque 1,2-3,0 Nm extra slim 1 Tool Finder
05006609001 - 4013288229953

Wera Werkzeuge GmbH
Korzerter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de