

Pocket-sized Residential Digital Multimeter

multicomp PRO

**RoHS
Compliant**



Description

This is a pocket-sized residential multimeter designed for home use. The compact structure makes it easy to hold in one hand, and the EBTN screen allows users to obtain clear readings at maximum angle, it is also great for working in dark environments.

Features

Display Count	: 4000
Low Battery Indication	: $\leq 2.7V$
Auto Power Off	: 15Min
Operation Temperature	: 0°C to 40°C
Safety	: CAT III 600V
Auto Range	: \checkmark
NCV	: \checkmark
Continuity Test	: \checkmark
Acousto-optic indication (NCV/continuity/battery power)	: \checkmark
Data Hold	: \checkmark
CE/ROHS	: \checkmark

Electrical Specifications

DC Voltage	: 4V/40V/400V/600V $\pm(0.5\%+2)$
AC Voltage	: 4V/40V/400V/600V $\pm(1.0\%+3)$
Resistance	: 400 Ω /4k Ω /40k Ω /400k Ω /4M Ω /20M Ω $\pm(0.8\%+2)$
Temperature	: -40° to 300°C / -40°F to 572°F $\pm 4^\circ C$

General Characteristics

Power	: 1.5V Battery (R03) $\times 2$
Display	: 44mm \times 26mm
Colour	: Green and Grey
Net Weight	: 130g
Size	: 130mm \times 65m \times 28mm
Warranty	: 12 Months

Accessories	Qty.	Note
Operating Manual	1 piece	-
Test Leads	1 pair	UL1032 20AWG PVC double insulated cable CAT III 600V 10A 800mm
Temp Probe	1 piece	Cross point thin line 1000 K type
Battery	2 pieces	1.5V AAA $\times 2$, replaceable

Newark.com/multicomp-pro
Farnell.com/multicomp-pro
sg.element14.com/b/multicomp-pro

multicomp PRO

Pocket-sized Residential Digital Multimeter

multicomp PRO

Part Number Table

Description	Part Number
Pocket-sized Residential Digital Multimeter, 4V AC/DC to 600V AC/DC	MP730425

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro
Farnell.com/multicomp-pro
sg.element14.com/b/multicomp-pro

multicomp PRO