



Laptop Ready

Power Charger 65W GaN US

GaN
Technology

PD
POWER DELIVERY
FAST CHARGE



Small & powerful 65 W PD charging of
3 USB devices (2 x USB C, 1 x USB A)

This ultra-small, high powered Power Charger USB-C 65 W GaN PD US from SKROSS® conveniently ensures a full battery, charging your laptop or USB device (2 x USB C, 1 x USB A) with 65 W of power. Compatible in more than 50 destinations with the US socket standard. Using Power Delivery (PD), it is easily able to power up a laptop, smartphone, tablet, audio device and more, ultra-fast. Featuring an ultra-small size using the latest GaN technology.

Suitable for



Compatibility (Output)



USA/Japan

Packaging (Retail)



ACTUAL SIZE



Product Category

- Tech / PD USB Wall Charger

Technical Specifications

- Suitable in all countries with US socket standard
- 1 x 65 W GaN PD Wall Charger (2 x USB Type-C, 1 x USB Type-A)
- **USB Output**
 - 1 x USB Type-C1 (PD) Output: 5.0 V DC / Max. 3.0 A, 9.0 V DC / Max. 3.0 A, 12.0 V DC / Max. 3.0 A, 15.0 V DC / Max. 3.0 A, 20.0 V DC / Max. 3.25 A, Max. 65.0 W
 - 1 x USB Type-C2 (PD) Output: 5.0 V DC / Max. 2.4 A, 9.0 V DC / Max. 2.22 A, 12.0 V DC / Max. 1.67 A, Max. 20.0 W
 - 1 x USB Type-A Output: 5.0 V DC / Max. 2.4 A, 9.0 V DC / Max. 2.0 A, 12.0 V DC / Max. 1.5 A, Max. 18.0 W
 - Dual Port Output USB-C1 + USB-C2: 45.0 W + 20.0 W
 - Dual Port Output USB-C1 + USB-A: 45.0 W + 18.0 W
 - Dual Port Output USB-C2 + USB-A: 5.0 V DC / 2.4 A (12.0 W)
 - Triple Port Output USB-C1 + USB-C2 + USB-A: 45.0 W + 12.0 W, 2.4 A (Max. 57.0 W)
 - Average active efficiency: 89.1%, Efficiency at low load (10 %): 83.75 %, No-load power consumption: 0.23 W
- USB output: Max. 65.0 W in total
- Input: 100 V – 240 V~, 50/60 Hz, 1.5 A

Weight

- Charger: 88 g
- Charger + packaging: 140 g

Dimensions

- Charger: W 42 mm H 60 mm D 30 mm
- Charger + packaging: W 95 mm H 180 mm D 35 mm

Packaging Unit

- Master retail: 20 pcs | Inner carton: 10 pcs
- Dimensions master retail: W 230 mm H 225 mm D 420 mm
- Pallet: 1400 pcs.

Standard Colour

- White

Description

Power Charger 65W GaN US, retail, white

Article-No.

SKCH001265WPDUSCN

EAN-Code

7640166328070

Made in China