Specifications





## Outlet grille - plastic - cut out 291x291mm - ext. dim 336x316mm - IP54

NSYCAG291LPF

#### **Overview**

Lead time

Usually Ships within 4 Weeks

#### Main

mann	
Range	ClimaSys
Product	ClimaSys CA
Range compatibility	Prisma Prisma P Prisma Prisma G
Product or component type	Outlet grille
Accessory / separate part category	Thermal management accessory
Accessory / separate part destination	ClimaSys ventilation system
Fixing mode	By screws Clipped
Device composition	1 support frame 1 external part 1 G2 M1 synthetic standard filter

## Complementary

Material	Injected thermoplastic (ASA PC)
Colour	External part: grey (RAL 7035)
cut-out dimensions	291 x 291 mm
Height	External: 336 mm
Width	External: 316 mm
Depth	External : 18 mm

#### **Packing Units**

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	5.000 cm
Package 1 Width	32.500 cm
Package 1 Length	34.500 cm
Package 1 Weight	827.000 g
Unit Type of Package 2	CAR
Number of Units in Package 2	6
Package 2 Height	40.000 cm

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Package 2 Width	30.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	5.408 kg
Unit Type of Package 3	P12
Number of Units in Package 3	144
Package 3 Height	131.000 cm
Package 3 Width	80.000 cm
Package 3 Length	120.000 cm
Package 3 Weight	145.000 kg

## **Contractual warranty**

Warranty

18 months

# Sustainability Screen Premium

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

## Well-being performance

Reach Free Of Svhc
Toxic Heavy Metal Free
Mercury Free
Rohs Exemption Information Yes

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations