




- Suitable for a main distribution board with two residual current breakers (RCB); includes all required components for wiring supply terminal blocks and connecting 14 AC circuits and two three-phase circuits.
 - Distribution of ground fault potentials via two 10 x 3 mm N-busbars; separation of N-potentials for insulation resistance measurement via N-disconnect slide links within the multilevel installation terminal block
- Contains:
- 16 x multilevel installation terminal block; NT/L/PE; 4 mm² (2003-7641)
 - 2 x multilevel installation terminal block; L/L; 4 mm² (2003-7642)
 - 2 x end and intermediate plate (2003-7692)
 - 3 x 2-conductor supply terminal block for distribution boxes; gray; 16 mm² (2016-7601)
 - 1 x 2-conductor supply terminal block for distribution boxes; blue; 16 mm² (2016-7604)
 - 1 x 2-conductor ground terminal block; green-yellow; 16 mm² (2016-7607)
 - 1 x end and intermediate plate (2016-7692)
 - 2 x 1-conductor N-disconnect terminal block; blue; 16 mm² (2016-7714)
 - 1 x end and intermediate plate (2016-7792)
 - 1 x screwless end stop; 10 mm wide (249-117)
 - 2 x busbar carrier; with end stop function (2009-305)
 - 1 x busbar; tin-plated; 0.2 m (210-133)
 - 1 x cover for busbar; transparent; 0.2 m (777-303)
 - 1 x marking strip; white; 0.5 m (2009-110)
 - 1 x WMB marker card; 1 ... 50 (793-5566)
 - 1 x WMB marker card; L1, L2, L3, N, PE (793-5472)
 - 1 x felt-tip pen (210-110)
- Assembly width incl. end stop: 20.52 cm

This item includes:					
					
Item No.: 210-110	1	Item No.: 249-117	1	Item No.: 777-303	1
Fiber-tip pen		Screwless end stop; 10 mm wide; for DIN-rail 35 x 15 and 35 x 7.5; gray		N-busbar cover; 1000 mm long; transparent	
					
Item No.: 793-5566	1	Item No.: 2003-7641	2	Item No.: 2003-7642	2
WMB marking card; as card; MARKED; 1 ... 50 (2x); stretchable 5 - 5.2 mm; Horizontal marking; snap-on type; white		Multilevel installation terminal block; with operating slots; 2.5 mm ² ; with N-disconnect slide link; NT/L/PE; Push-in CAGE CLAMP®; 2,50 mm ² ; gray		Multilevel installation terminal block; with operating slots; 2.5 mm ² ; L/L; Push-in CAGE CLAMP®; 2,50 mm ² ; gray	
					
Item No.: 2009-110	2	Item No.: 2009-305	2	Item No.: 2016-7601	3
				Item No.: 2016-7604	1



This item includes:			
Marking strips; for Smart Printer; on reel; not stretchable; plain; snap-on type; white		Busbar carrier; with end stop function and detachable separator plate; for DIN 35 rail; 7.5 mm thick; blue	
			
Item No.: 2016-7607	1	Item No.: 2016-7692	1
2-conductor ground terminal block; 16 mm²; side and center marking; for DIN-rail 35 x 15 and 35 x 7.5; Push-in CAGE CLAMP®; 16,00 mm²; green-yellow		End and intermediate plate; 1 mm thick; orange	
			
Item No.: 210-133			
Busbar; tin-plated; 1000 mm long; Cu 10 mm x 3 mm; white			
			

Material data	
Note (material data)	Information on material specifications can be found here
Fire load	8.702 MJ
Weight	660.9 g

Commercial data	
Product Group	22 (TOPJOB S)
eCl@ss 10.0	27-14-11-25
eCl@ss 9.0	27-14-11-25
ETIM 8.0	EC001329
ETIM 7.0	EC001329
PU (SPU)	1 pcs
Packaging type	Box
Country of origin	QU
GTIN	4045454962272
Customs tariff number	80808080888

Environmental Product Compliance	
CAS-No.	7439-92-1
REACH Candidate List Substance	Lead
RoHS Compliance Status	Compliant, No Exemption
SCIP notification number (Austria)	2da59418-7ef6-4dd3-a247-1c9607c892e5
SCIP notification number (Belgium)	1a83b7aa-5af1-49f7-b160-68f818017884
SCIP notification number (Bulgaria)	0ebdbfb4-461b-4f9b-8947-30ddf116a737
SCIP notification number (Czech Republic)	55244556-901a-471e-9194-07a28fb3d98e
SCIP notification number (Denmark)	ef0d3e7c-1912-4462-a7bf-6c225283214f
SCIP notification number (Finland)	8d452fc1-9050-4bd2-8ae9-751d63fdc03c
SCIP notification number (France)	91d8660e-992c-4f4c-b7d9-455b3a3d8902
SCIP notification number (Germany)	06281839-5f05-45f9-8837-d33f944eb98f
SCIP notification number (Hungary)	09225464-cf90-4653-a831-6d38f8637e10
SCIP notification number (Italy)	6f741b7c-180b-4275-b4c6-984b7eec481f
SCIP notification number (Netherlands)	141174ee-fe6f-4d2d-9c65-ea7d71f16a78
SCIP notification number (Poland)	c597f6ad-dcad-44e7-bc81-8a1846f71745
SCIP notification number (Romania)	28bdba87-569b-4d71-92e0-2b9b25d50312
SCIP notification number (Sweden)	3c1a87a7-6b24-4e92-9fa5-f44c3f68aee9



Downloads		
Environmental Product Compliance		
Compliance Search		
Environmental Product Compliance 821-122		

Documentation		
Additional Information		Bid Text
Technical Section	pdf 2246.92 KB	
		ausschreiben.de 821-122 

CAD/CAE-Data	
CAE data	
WSCAD Universe 821-122	