STI Enviro Stopper®











PRODUCT OVERVIEW

A protective cover that is ideal for extending the life and reliability of devices exposed to harsh environments. It offers protection to manual call points and switches against dust and water ingress both outside and inside, as well as preventing tampering, vandalism and damage from accidental or malicious operation.

HOW IT WORKS

Easy to install, the Enviro Stopper consists of a clear, tamperproof, tough polycarbonate cover and back box that can accommodate a standard European call point or switch. When the cover is closed, the unit is sealed and achieves a rating of IP66/56, preventing dust, grime and water getting to the device.

KEY FEATURES

General Information

- Protective cover is ideal for extending the life and reliability of devices exposed to harsh environments.
- Three year guarantee against breakage of polycarbonate in normal use (one year on electromechanical and electronic components).

Design

- Option 6 Cover, back box and sealed mounting plate achieves IP66 (back box) and IP56 (cover) rating.
- Option 7 Cover, back box and open mounting plate achieves IP56 (back box) and IP56 (cover) rating.

Construction

· Tough polycarbonate housing can withstand the severest of knocks.

Installation

- · Ideal for use in wet or wash down areas, overall rating of IP56/IP66 for the back box.
- · Can accommodate a standard European call point or switch.
- · Typical working properties of polycarbonate are -40° to 121°C (-40° to 250°F).

Electronics

 Available with or without a 95 dB integral sounder, powered by a 9V PP3 battery (included).


Options

- One breakseal is supplied with each model. Additional breakseals are available for added security.
- · Available in a range of colours.
- · Custom labelling available.





STI Enviro Stopper®

Dimensions and Technical Information



TEXT HERE LIFT HERE Locking tab 114mm Front View





MODELS AVAILABLE

STI-13610FR Enviro Stopper, (EU enclosed plate & frosted back box) without

integral sounder, with ACTIVATE FIRE ALARM label.

STI-13620FR Enviro Stopper, (EU enclosed plate & frosted back box) with

integral sounder, with ACTIVATE FIRE ALARM label.

Accessories:

STI/BS Break Seals (Quantity. 10)
KIT-319 Wiring harness for remote power

KIT-EA135 Servicing pin

STI-6602 Replacement Sounder Unit

APPROVALS

- ADA Compliant
- Cover option '3' only has been tested and approved or listed by:
- UL/CUL Listed No. \$2466

Back box, open mounting plate - IP Rating, 56 Back box, sealed mounting plate - IP Rating, 66



Taylor House 34 Sherwood Road Bromsgrove Worcestershire B60 3DR, England Tel: +44 (0)1527 520 999 Fax: +44 (0)1527 501 999 info@sti-emea.com www.sti-emea.com 2306 Airport Road Waterford, Michigan 48327, USA Tel: 248-673-9898 Fax: 248-673-1246 info@sti-usa.com www.sti-usa.com