

**RoHS  
Compliant**



Glue Gun

## Description

This is a high power 50W glue gun featuring an ergonomic handle and high temperature for use with 7mm glue sticks.

## Features

- Drip control function
- For use with 7mm glue sticks
- Supplied with standard UK/EU plug

## Specification

Power	: 50W
Voltage	: 230V AC
High temperature	: 180°C
Warranty	: 03 years

## Extension Cords

Use completely unrolled and safe extension cords with a capacity of at least 5 Amps.

## Getting Started

The module allow glue gun to reach operating temperatures before using ( $\pm 5$ mins). Insert the glue stick. Press the feed trigger.

White Transparent  $\varnothing 7 \times 100$ mm

Black Transparent  $\varnothing 7 \times 100$ mm

### Drip-Control Function

When heated up, the glue gun has a drip-control function. This prevents the glue from dripping when the glue gun is at operating temperature.

**Notes:** During heating-up the glue gun may release a few drops of glue. Do not use glitter or colour sticks at high temperature. The drip-control function will not work properly.

### Change Glue Sticks

Do not attempt to remove the unused portion of the glue stick from your glue gun. If you need to switch glue stick formulas, empty the melting chamber by squeezing the trigger and insert new formula.

### Stand / Kick Stand

When glue gun is hot, do not lay on its side.

Always use stand.

Push stand into "down" position when temporarily not in use. When re-suing or storing, push stand back into "up" position.

## Cleaning

Before any work on the unit itself, pull the mains plug.

Always keep the unit dean so that it functions properly and accurately.

## Used Symbols



Read These Instructions



Class II Constructed



Do not dispose of electric tools, accessories and packaging together with household waste material.

Working safely with this unit is possible only when the operating and safety information are read completely and the instructions contained therein are strictly followed.

- If the cable is damaged or cut through while working, do not touch the cable but immediately pull the mains plug. Never use the unit with a damaged cable.
- If the supply cord is damaged, it must be replaced by the manufacturer, its service agent or similarly qualified persons in order to avoid a hazard.
- For indoor use only.
- Connect units that are used outdoors by means of a fault current protection switch (FI) with a maximum triggering current of 30mA. Use only an extension cable that is approved for outdoor use.
- Always direct the cable to the rear away from the unit.
- For pauses in the work of more than 30 minutes pull the mains plug.
- Children shall not play with the appliance.
- Cleaning and user maintenance shall not be made by children without supervision.
- Manufacturer is able to ensure flawless functioning of the unit only if the original accessories intended for it are used.
- Do not work materials containing asbestos (asbestos is considered carcinogenic).
- Take protective measures when during work dust can develop that is harmful to one's health, combustible or explosive (some dust mask are considered carcinogenic); wear a dust mask and work with the dust I chip extraction when connectable
- Do not change nozzles while glue gun is in "on" position, plugged in, or warm to the touch. Before changing nozzles, make sure glue gun is cool to the touch, unplugged, and the switch is in the "off" position.

## Environment

### Disposal

The unit, accessories and packaging should be sorted for environment-friendly recycling.

### Only For European Countries



Do not dispose of power tools into household waste! According to the European Guideline 2012/19/EC for Waste Electrical and Electronic Equipment and its implementation into national right, power tools that are no longer usable must be collected separately and disposed of in an environmentally correct manner.

## Service And Warranty

This product is guaranteed in accordance with statutory/country specific regulations; damage due to normal wear and tear, overload or improper handling will be excluded from the guarantee. If the unit should fail despite the care take in manufacturing and testing, send it dismantled together with proof of purchase to your dealer.

## Glue Sticks



## Features

- For use with hot melt glue gun
- Glue stick dimensions:  $\varnothing 7\text{mm} \times 100\text{mm}$

## Part Number Table

Description	Part Number
Hot Melt Glue Gun, 50W, 180°C, EU Plug	MP740843
Hot Melt Glue Gun, 50W, 180°C, UK Plug	MP740844
Glue Sticks, White Transparent, $\varnothing 7\text{mm} \times 100\text{mm}$	MP740845
Glue Sticks, Black Transparent, $\varnothing 7\text{mm} \times 100\text{mm}$	MP740846

**Important Notice :** This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.