

Plunge Cut Circular Saw XGT®

SP001GZ03

40Vmax • 165 mm • 2 500 – 4 900 min⁻¹

Brushless XGT® plunge cut circular saw for professional use

Precise XGT® 40Vmax Plunge cut circular saw for professional use. Auto-start Wireless System (AWS) connects to vacuum cleaner with Bluetooth. eXtreme Protection Technology (XPT) is engineered for improved dust and water resistance for operation in harsh conditions. Tool only, battery and a charger not included.





Technical specifications

Voltage XGT \
Nominal Battery Voltage 40 V
Battery Chemistry (Ni-Cd / Ni-MH / Li-ion ion)

No load speed 2500 - 4900 min⁻¹

Max. Cutting Depth at 90°

Max. Cutting Depth at 45°

Max. Cutting Depth at 45°

Max. Cutting Depth at 48°

Max. Bevel Range (Right)

Blade Diameter

Bore Size (Arbor Diameter)

Electronic brake

AWS ready

56 mm

40 mm

Sound Power Level (L_{WA}) 100 dB(A)

Sound Pressure Level (L_{DA}) 92 dB(A)

Noise Uncertainty (K Factor) 3 dB(A)

User benefits

- Auto-start Wireless System (AWS) connects to compatible vacuum cleaners with Bluetooth
- Constant speed control provides consistent surface finish
- Precision accurate cutting delivers a splinter free mirror finish
- Soft start for smooth start-ups
- Easy to set depth adjustment with large scale
- Brushless motor is electronically controlled to optimise battery energy use for longer run time per charge
- Battery protection system automatically shuts off power when the battery level is low



EAN 0088381749350

Link to product - www.makitauk.com



Related products

Standard AC

B-57336

Circular saw blade, Efficut T.C.T, 165

821552-6

Makpac case (4)



783203-8

Hex Wrench 5 Mm



Standard MA

198900-7

Bluetooth Chip



Optional AC

165447-6

Parallel Guide

194367-7

Guide rail, 3 000 mm

196664-7

Bevel guide set



198885-7

194385-5

Clamp set

Guide rail joint connector set, 2 pcs

199140-0

199826-6

Guide rail, 1 000 mm



199141-8

Guide rail, 1 500 mm

821552-6

Makpac case (4)



783203-8 Hex Wrench 5 Mm

8351E4-2

839290-6

MakPac (4) Inlay



B-33685

Circular Saw Blade, Specialized,

Makpac Type 4 Inner Tray

B-56699

Circular saw blade, Specialized T.C.T,

Quick-Release Ratcheting Guide Rail



B-56708

Circular saw blade, Specialized T.C.T,



B-56720

Circular saw blade, Specialized T.C.T,



B-56742

Circular saw blade, Specialized T.C.T,





E-05664

Guide Rail Protective Holder

E-12217

Circular Saw Blade, Efficut T.C.T, 165



E-12223

Circular Saw Blade, Efficut T.C.T, 165



Other

User manual

Parts drawing