



SanDisk®

CREATOR PHONE SSD

Make your creative production portable with the SanDisk® Creator Phone SSD.

Part of the SanDisk® Creator Series, the SanDisk® Creator Phone SSD is designed for producing content on the go, attaching effortlessly to your MagSafe-compatible smartphone. Capture stunning 4K at 60fps videos in Apple ProRes and save content directly to your drive to start editing instantly. Rugged and reliable for wherever inspiration takes you, your drive features a durable silicone shell, up to three-meter drop protection,³ and IP65 water and dust resistance.⁴ And to streamline your editing process, enjoy one included month of Adobe Creative Cloud.⁵ SanDisk® gives you the tools you need for whenever inspiration strikes.

HIGHLIGHTS

- **FOR CREATORS WITH A VISION.** Amplify your creative voice with a collection of products that elevate every step of your workflow.
- **SHOOT WITH APPLE PRORES 4K.** Your drive supports video capture in Apple ProRes 4K at 60fps. For quick editing, save your content directly to your drive.
- **PRODUCTIVITY PERKS.** Enjoy one included month of Adobe Creative Cloud.⁵
- **READY FOR ADVENTURE.** Be prepared wherever inspiration strikes with a durable silicone shell, up to three-meter drop protection,³ and IP65 water and dust resistance.⁴
- **FOR YOUR GEAR.** Thanks to exFAT formatting, your drive is compatible out of the box with Windows®, Android™, and macOS devices.
- **MAGSAFE COMPATIBLE.** Easily attach your drive to your compatible smartphone using MagSafe for an instant mobile production rig.

SanDisk®

CREATOR PHONE SSD

Make your creative production portable with the SanDisk® Creator Phone SSD.



PRODUCT SPECIFICATIONS

FORM FACTOR	EXTERNAL SSD
AVAILABLE CAPACITIES ¹	2TB, 1TB
INTERFACE	USB TYPE-C™ (USB 3.2 GEN 2)
DATA TRANSFER RATES ²	UP TO 1000MB/S READ SPEEDS; UP TO 950MB/S WRITE SPEED
PRODUCT DIMENSIONS	3.25 x 2.69 x 0.43 IN 82.5 x 68.4 x 11 MM
PACKAGING DIMENSIONS	1.30 x 4.21 x 5.00 IN 33.00 x 107.00 x 127.00 MM
PRODUCT WEIGHT	0.12 LB 54 G
OPERATING TEMPERATURE	0°C TO 45°C 32°F TO 113°F
NON-OPERATING TEMPERATURE	-20°C TO 85°C -4°F TO 185°F
COMPATIBILITY	COMPATIBLE WITH A RANGE OF USB TYPE-C™ DEVICES (E.G., SMARTPHONES, LAPTOPS, TABLETS)
SYSTEM REQUIREMENTS	WINDOWS® 10+, MACOS 14+, IOS/IPADOS 17+, ANDROID™ 14+, FORMATTED WITH EXFAT FOR COMPATIBILITY
LIMITED WARRANTY ⁵	5-YEAR LIMITED

¹ 1TB=1,000,000,000,000 bytes. Actual user storage less.

² Up to 1000MB/s read speed; up to 950MB/s write speed. Based on internal testing; performance may be lower depending upon host device, usage conditions, and other factors. 1MB = 1,000,000 bytes.

³ Based on internal testing.

⁴ IEC 60529 IP65: Tested to withstand water flow (30 kPa) at 3 min.; limited dust contact does not interfere with operation. Must be clean and dry before use.

⁵ Individual membership. Internet connection and Adobe ID required. Not available in all countries. Offer limited to 1 per SanDisk Creator product purchase; subject to acceptance of applicable Terms of Use. Offer must be redeemed by April 30, 2026, or while activation code supplies last. SanDisk reserves the right to change or discontinue this offer at any time without notice. See www.sandisk.com/creator-cc for applicable legal terms and privacy policy.

SanDisk and the SanDisk logo are registered trademarks or trademarks of SanDisk Corporation or its affiliates in the US and/or other countries. Android is a trademark of Google LLC. macOS, iOS, iPadOS, iPhone and MagSafe are trademarks of Apple Inc. USB Type-C is a trademark of USB Implementers Forum. Windows is a trademark of the Microsoft Corporation. Adobe and Creative Cloud are either registered trademarks or trademarks of Adobe in the United States and/or other countries. All other marks are the property of their respective owners. Product specifications subject to change without notice.

© 2025 SanDisk Corporation or its affiliates. All rights reserved.