

3ft (1m) Durable USB-C to Lightning Cable - Right-Angled Heavy Duty Aramid Fiber USB Type-C to Lightning Charging/Sync Cord - Apple MFi Certified - Rugged iPhone Lightning Cable

Product ID: RUSB2CLTMM1MR



Establish a right angle connection to a Lightning-enabled device (e.g., iPhone, iPad, iPad Mini, and some iPods) and to a USB Type-C power source, using this 3ft (1m) Durable USB-C to Lightning cable.

The durable Lightning charging cable features aramid fiber reinforcement that enhances tensile strength, abrasion resistance, and resistance to cable stress. This reinforced cable is able to flex without over-stretching. In addition, the connectors feature metal shells covered in fully-molded TPE for improved connector longevity.

The USB Type-C to right-angled Lightning cable has been designed to prevent cable/connector strain. The extra-long strain relief moldings have been assessed to withstand over 5,000+ bend cycles at a 180 angle.

The durable USB-C to right-angled Lightning cable supports USB 2.0 (480Mbps) specifications. It is Apple MFi certified which guarantees up to 3A fast charging and reliable data sync from USB-C charging ports.

This product is backed for 2 years, including free lifetime 24/5 multi-lingual technical assistance.

Certifications, Reports and Compatibility



Applications

Features

- **RIGHT ANGLE LIGHTNING CABLE:** 3ft (1m) USB-C to Lightning charging cable features a right angle Lightning connector; Ideal for tight spots allowing the cable to run flush with the device; Reduces strain on the port and connector vs. a straight cable
- **RUGGED DESIGN:** USB Type-C to Lightning cable reinforced with aramid fiber for increased tensile strength; Tested to withstand 10000+ insertions and 5000+ bend cycles at 180 angle; Durable TPE jacket, connector body/shell, and strain reliefs
- **FAST CHARGE AND SYNC:** Fast charging of up to 3A from a USB port or Quick Charge enabled port/power adapter; This high-quality cord is designed to charge and sync Lightning devices
- **APPLE MFI CERTIFIED:** Lightning adapter cable guarantees reliable fast charge and sync from a USB Type C charging port; For Lightning devices including iPhone 14 Pro/14/13 Pro/13/12 Pro/12/Max/Mini, iPhone 11 Pro/11, iPhone XR, iPad Air, iPad, iPad Mini
- **SPECS:** Length: 3ft (1m); Color: Black; Connectors: Male USB-C to Male Lightning; Performance: USB 2.0; Braid Material: Aramid Fiber; Power: Up to 3A; Jacket Type: TPE; Shielding: EMI Protection with Aluminum/Mylar

Hardware

Warranty	2 Years
Connector Plating	Gold and Nickel
Cable Jacket Material	TPE - Thermoplastic Elastomers
Cable Shield Material	Aluminum-Mylar Foil with Braid

Performance

Maximum Cable Length	39.4 in [1000 mm]
Type and Rate	USB 2.0 - 480 Mbit/s

Connector(s)

Connector A	1 - USB Type-C (24-pin) USB 2.0 (480Mbps)
Connector B	1 - Apple Lightning Connector C94 (8-pin)

Environmental

Operating Temperature	0 to 50C (32 to 122F)
Storage Temperature	0 to 50C (32 to 122F)
Humidity	0 to 85% RH

Physical Characteristics

Color	Black
-------	-------

Connector Style	Right Angle to Straight
Wire Gauge	22/32 AWG
Cable Length	3.3 ft [1 m]
Cable OD	0.1 in [3.1 mm]
Product Length	3.3 ft [1.0 m]
Product Width	0.8 in [2.0 cm]
Product Height	0.2 in [0.6 cm]
Weight of Product	0.8 oz [23.0 g]

Packaging Information

Package Quantity	1
Package Length	5.5 in [14.0 cm]
Package Width	5.0 in [12.6 cm]
Package Height	0.6 in [1.4 cm]
Shipping (Package) Weight	1.1 oz [30.0 g]

What's in the Box

Included in Package	1 - USB-C to Right Angle Lightning Cable
---------------------	--

****Product appearance and specifications are subject to change without notice.***