



# Data Sheet | Item Number: 221-2534

Mounting carrier; 4-way; for inline splicing connector with lever; with snap-in mounting foot; gray

<https://www.wago.com/221-2534>



Color: ■ gray





| Physical data           |  |                         |
|-------------------------|--|-------------------------|
| Width                   |  | 38.8 mm / 1.528 inches  |
| Height                  |  | 11.03 mm / 0.434 inches |
| Height from the surface |  | 6.5 mm / 0.256 inches   |
| Depth                   |  | 56 mm / 2.205 inches    |

| Mechanical data |  |              |
|-----------------|--|--------------|
| Design          |  | 4-way        |
| Mounting type   |  | Snap-in foot |

| Material data                      |  |                                                                          |
|------------------------------------|--|--------------------------------------------------------------------------|
| Note (material data)               |  | <a href="#">Information on material specifications can be found here</a> |
| Color                              |  | gray                                                                     |
| Material group                     |  | I                                                                        |
| Insulation material (main housing) |  | Polyamide (PA66)                                                         |
| Flammability class per UL94        |  | V0                                                                       |
| Fire load                          |  | 0.186 MJ                                                                 |
| Weight                             |  | 6.2 g                                                                    |

| Commercial data       |  |               |
|-----------------------|--|---------------|
| PU (SPU)              |  | 25 (5) pcs    |
| Packaging type        |  | Box           |
| Country of origin     |  | CN            |
| GTIN                  |  | 4066966120004 |
| Customs tariff number |  | 39269097900   |

| Product classification |  |                      |
|------------------------|--|----------------------|
| UNSPSC                 |  | 39121702             |
| ETIM 9.0               |  | EC002848             |
| ETIM 8.0               |  | EC002848             |
| ECCN                   |  | NO US CLASSIFICATION |

| Environmental Product Compliance |  |                        |
|----------------------------------|--|------------------------|
| RoHS Compliance Status           |  | Compliant,No Exemption |

| Downloads                                 |  |  |
|-------------------------------------------|--|--|
| Environmental Product Compliance          |  |  |
| Compliance Search                         |  |  |
| Environmental Product Compliance 221-2534 |  |  |

| CAD/CAE-Data                                                                      |                                                                                     |
|-----------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|
| CAD data                                                                          | CAE data                                                                            |
| 2D/3D Models<br>221-2534                                                          | EPLAN Data Portal<br>221-2534                                                       |
|  |  |
|                                                                                   | ZUKEN Portal<br>221-2534                                                            |
|                                                                                   |  |

| 1 Compatible Products        |
|------------------------------|
| 1.1 Optional Accessories     |
| 1.1.1 Installation           |
| 1.1.1.1 Mounting accessories |



**Item No.: 209-119**  
Fixing screw; for 209-120 mounting carrier

**Item No.: 209-123**  
Mounting foot with screw; can be screwed on terminal blocks with fixing flange; 6.4 mm wide; gray



**Item No.: 209-120**  
Mounting foot; can be snapped on terminal blocks with snap-in mounting foot; for mounting on relay-modules; 6.4 mm wide; gray

| 1.1.2 Marking         |
|-----------------------|
| 1.1.2.1 Marking strip |



**Item No.: 210-834**  
Marking strips; on reel; 5 mm wide; plain; Self-adhesive; white

| Installation Notes |
|--------------------|
| Installation       |




Place the inline splicing connector on the carrier in front of the mounting position.

Push the connector to the center position until it snaps into place.

Mounting carrier without strain relief – snapped onto DIN-rail

| Strain relief |
|---------------|
|---------------|



3-pole mounting carrier with strain relief



Various combinations of 1- to 5-connector mounting carriers are possible via side-by-side latching mechanism.