

1U 19 inch Server Rack Rails - 24-36 inch Adjustable Depth - Universal 4 Post Rack Mount Rails - Network Equipment/Server/UPS Mounting Rail Kit HPE ProLiant Dell PowerEdge

Product ID: UNIRAILS1UB



These 1U server rack rails let you mount devices, such as servers or networking equipment, that did not come with rack rails into your 19" 4 post rack. The adjustable server rack rails are also a great solution for mounting OEM equipment such as Dell, IBM, HP or Apple servers.

Adhering to the EIA/ECA-310 standard for 19 inch server rack equipment and accessories, these mounting rails are compatible with most 19 inch server racks. The depth is adjustable for a variety of rack sizes and configurations up to a maximum depth of 36 inches.

To ensure your equipment is secure, these universal rack mount rails feature cold-rolled steel construction. The durable design can support a weight load of up to 200 lbs (90 kg).

StarTech.com conducts thorough compatibility and performance testing on all our products to ensure we are meeting or exceeding industry standards and providing high-quality products to IT Professionals. Our local StarTech.com Technical Advisors have broad product expertise and work directly with our StarTech.com Engineers to provide support for our customers both pre and post-sales.

The UNIRAILS1UB is backed by a lifetime StarTech.com warranty with free technical support.

Certifications, Reports and Compatibility



Applications

- Mount rackmount equipment that is missing its original rails

- Use to rackmount OEM equipment such as Dell, IBM, HP or Apple servers that no longer have rack rails available for purchase
- Securely mount non-rackmount equipment into any 19" EIA/ECA-310 server rack

Features

- **UNIVERSAL SERVER RACK RAILS:** Installs in 4-post EIA/ECA-310 rack to mount any 19" device like server or UPS; Ideal replacement for lost rails on HPE ProLiant/Dell PowerEdge/Lenovo ThinkSystem/APC UPS
- **HASSLE-FREE INSTALLATION:** 1U network rack rail kit with a 24-36in adjustable depth and mounting hardware included, these rails are easy to install; Your device securely rests on the rails
- **DURABLE:** Constructed from cold rolled steel for strength and featuring a matte black finish for aesthetic, these rails support a generous weight capacity of 200 lbs., to easily mount any 19" device
- **SPECS:** Universal 19 inch EIA/ECA-310 compliant design Adjustable depth: 24-36in. Weight capacity: 200 lbs. (90 kg) 8 x M6 cage nuts and screws included
- **THE STARTECH.COM ADVANTAGE:** StarTech.com offers a 2-year warranty and free lifetime 24/5 technical support on these rails and has been the choice of IT professionals and businesses for over 30 years

Hardware

Warranty	Lifetime
U Height	1U
Cable Management	No
Industry Standards	EIA-310-D

Performance

Weight Capacity (Stationary)	200.0 lb [90.7 kg]
------------------------------	--------------------

Physical Characteristics

Color	Black
Material	Steel
Product Length	24.7 in [62.8 cm]
Product Width	3.1 in [8.0 cm]
Product Height	1.8 in [4.5 cm]

Weight of Product	7.7 lb [3.5 kg]
Maximum Mounting Depth	36.0 in [91.4 cm]
Minimum Mounting Depth	24.0 in [61 cm]

Packaging Information

Package Quantity	1
Package Length	8.9 in [22.6 cm]
Package Width	25.4 in [64.5 cm]
Package Height	3.9 in [10.0 cm]
Shipping (Package) Weight	8.5 lb [3.9 kg]

What's in the Box

Included in Package	2 - Universal Rack Rails
	8 - M6-12 Screws
	8 - M6 Cage Nuts
	8 - M6 Plastic Cup Washers
	1 - Quick Start Guide

Warranty Information

Warranty	Lifetime
----------	----------

****Product appearance and specifications are subject to change without notice.***