



Charge 'n' Go Power Bank with Stand Magnetic Wireless 10000mAh

PN: 32259, 32264, 32266, 32267, 32268

Description

Compact & Powerful: The Verbatim Charge 'n' Go Power Bank, with 10,000mAh capacity is your portable powerhouse, delivering reliable energy in a sleek, easy-to-carry design. Whether it's charging smartphones, tablets, or speakers, its high capacity keeps you and your devices powered through travel, commutes, events, or outdoor adventures. Ideal for anyone needing fast, on-the-go power.

Versatile Dual Charging Mode: With 15W magnetic wireless charging and 20W USB-C PD fast charging via USB-C port, this power bank is as versatile as your lifestyle. MagSafe compatibility makes wireless charging effortless for iPhones, while Android phones users enjoy the same convenience*. Whether you're commuting, camping, or working remotely, this power bank ensures your devices stay powered up quickly and efficiently.

Built-in Foldable Stand for Hands-Free Use: For added convenience, the built-in foldable stand lets you set up your phone at the perfect angle, in portrait or landscape mode, while it charges. Whether you're watching a movie, taking video calls, or following a recipe, you can enjoy hands-free use with ease.

Smart, Bi-directional Charging: With a bi-directional USB-C port, this power bank handles charging in and out through a single port, simplifying your charging routine. The LED power indicator lets you know exactly how much power you have left, keeping you in control and worry-free.

Trusted On-the-Go Energy: Your safety is our priority. The Charge 'n' Go Power Bank is designed with 6 essential protection systems—FOD, overcurrent, short circuit, over charge voltage, over discharge voltage and over-temperature protection—ensuring a secure charging environment for all your devices.

Accessories Included: Each power bank includes a USB-C to USB-C cable and a magnetic metal ring for extra support, so you can attach it securely to your phone or case whenever needed.

*Charging power varies: iPhone up to 7.5W, Android phones up to 15W, depending on device protocols.



Charge 'n' Go Power Bank with Stand Magnetic Wireless 10000mAh

PN: 32259, 32264, 32266, 32267, 32268

Product Specifications

- Battery Capacity: 10000mAh
- Rated Capacity: Based on 5V-2.4A output : Around 6000mAh
- Chemistry of Battery: Li-polymer battery cell
- USB-C PD 3.0 Input: 5 V = 3 A, 9 V = 2 A (18 W max.)
- USB-C PD 3.0 Output: 5 V = 3 A, 9 V = 2.22 A, 12 V = 1.67 A (20 W max.)
- Wireless Charging: 5 W, 7.5 W, 10 W, 15 W (15 W max.)
- Total PD Output: 20 W max.
- Supports PD 3.0, QC 3.0, Apple 2.4A, BC1.2, DCP, AFC
- Safety Protection: FOD / Short circuit / Over current / Over temperature / Over charge voltage / Over discharge voltage protection
- Working Temperature: 0 to 35 °C
- Storage Temperature: Under normal temperature conditions: -10 to 45 °C; charging and discharging every 3-4months

Languages

Front of pack: English

Back of pack: English, French, German, Dutch, Italian, Spanish, Portuguese, Polish, Russian, Czech, Hungarian, Serbian, Croatian, Traditional Chinese, Simplified Chinese, Korean, Japanese

Quick Installation Languages

English, German + Technical support text in English, French, German, Dutch, Italian, Spanish, Portuguese, Polish, Russian, Czech, Hungarian, Serbian, Croatian, Traditional Chinese, Simplified Chinese, Korean, Japanese



PN	Qty	Colour	Pack Content:
32259	1	Green	<ul style="list-style-type: none">• Verbatim Charge 'n' Go Power Bank Magnetic Wireless 10000mAh• Metallic ring• USB-C® to USB-C® cable• Quick Start Guide
32264	1	Black	
32266	1	Blue	
32267	1	Pink	
32268	1	Grey	

Charge 'n' Go Power Bank with Stand Magnetic Wireless 10000mAh



Reorder No.	Description	Tariff Code	Barcode	EAN-128	EAN-14
32259	Charge 'n' Go Power Bank with Stand Magnetic Wireless 10000mAh – Green	85076000	023942322598	(02)00023942322597(37)1091843 (02)00023942322597(37)2091843	20023942322591 50023942322592
32264	Charge 'n' Go Power Bank with Stand Magnetic Wireless 10000mAh - Black	85076000	023942322641	(02)00023942322641(37)1091843 (02)00023942322641(37)2091843	20023942322645 50023942322646
32266	Charge 'n' Go Power Bank with Stand Magnetic Wireless 10000mAh - Blue	85076000	023942322665	(02)00023942322665(37)1091843 (02)00023942322665(37)2091843	20023942322669 50023942322660
32267	Charge 'n' Go Power Bank with Stand Magnetic Wireless 10000mAh - Pink	85076000	023942322672	(02)00023942322672(37)1091843 (02)00023942322672(37)2091843	20023942322676 50023942322677
32268	Charge 'n' Go Power Bank with Stand Magnetic Wireless 10000mAh - Grey	85076000	023942322689	(02)00023942322689(37)1091843 (02)00023942322689(37)2091843	20023942322683 50023942322684



Charge 'n' Go Power Bank with Stand Magnetic Wireless 10000mAh



Reorder No.	32259	32264	32266	32267	32268
Product Dimensions L x W x H			107 x 71 x 15.5mm		
Product Weight			217.8 grams (approx)		
Units per Pack			1		
Pack Dimensions L x W x H			128 x 98 x 30mm		
Pack Weight			291 grams (approx)		
Units per Inner Carton (MOQ)			10		
Inner Carton Dimensions L x W x H			270 x 185 x 115mm		
Inner Carton Weight			300 grams (approx)		
Units per Outer Carton			20		
Outer Carton Dimensions L x W x H			290 x 205 x 265mm		
Outer Cartons Weight			6000 grams (approx)		
Outer Cartons per Layer			48		
Layers per Pallet			4		
Units per Pallet			960		