

▲ **ST04684** (for 37"-86" TVs)


Stylish
Full-Motion TV Wall Mounts

*Comprehensive Solutions
for a Refined Viewing Experience*






▲ **ST04682**

Stylish Full-Motion TV Wall Mounts



Easy to adjust
find the optimal viewing angle



Smooth Movement with Ample Range of Motion
effortlessly adjust to the optimal position for a better viewing experience


Easy to install
simply hang the TVs to the mounts

Stylish Full-Motion TV Wall Mounts


For Solid Wall and Single Stud

Dimensions(mm)


ST04679




ST04680



ST04681



ST04682



Item No.	ST04679	ST04680	ST04681	ST04682
Fit Screen Size	23"-43"	23"-43"	23"-65"	23"-65"
Weight Capacity	35kg (77lbs)	35kg (77lbs)	35kg (77lbs)	35kg (77lbs)
Max. VESA	200x200	200x200	400x400	400x400
Profile	58~230mm (2.3"~9.1")	48~418mm (1.9"~16.5")	63~235mm (2.5"~9.3")	53~423mm (2.1"~16.7")
Tilt Range	$+5^\circ$ ~- 10°	$+5^\circ$ ~- 10°	$+5^\circ$ ~- 10°	$+5^\circ$ ~- 10°
Swivel Range	$+90^\circ$ ~- 90°	$+90^\circ$ ~- 90°	$+90^\circ$ ~- 90°	$+90^\circ$ ~- 90°
Screen Leveling	$+3^\circ$ ~- 3°	$+3^\circ$ ~- 3°	$+3^\circ$ ~- 3°	$+3^\circ$ ~- 3°
Material	Steel, Plastic	Steel, Plastic	Steel, Plastic	Steel, Plastic



Stylish Full-Motion TV Wall Mounts

For Solid Wall and Double Stud


Dimensions(mm)

ST04683

ST04684



ST04685



Item No.	ST04683	ST04684	ST04685
Fit Screen Size	32"-75"	37"-86"	43"-95"
Weight Capacity	45kg (99lbs)	60kg (132lbs)	60kg (132lbs)
Max. VESA	400x400	600x400	800x400
Profile	67~482mm (2.6"~19")	65~480mm (2.6"~18.9")	65~480mm (2.6"~18.9")
Tilt Range	$+5^\circ$ ~- 10°	$+5^\circ$ ~- 10°	$+5^\circ$ ~- 10°
Swivel Range	$+60^\circ$ ~- 60°	$+60^\circ$ ~- 60°	$+60^\circ$ ~- 60°
Screen Leveling	$+3^\circ$ ~- 3°	$+3^\circ$ ~- 3°	$+3^\circ$ ~- 3°
Material	Steel, Plastic	Steel, Plastic	Steel, Plastic