

32-inch 16:9 Computer Monitor Privacy Screen, Hanging Acrylic Filter, Quick-Install Security Shield, Monitor Screen Protector, +/- 30 Deg. View, Glossy, TAA

**Product ID:** 3269A-PRIVACY-SCREEN



Designed for open-concept offices, hoteling setups, and shared workstations, this 32-inch privacy filter protects sensitive on-screen data from prying eyes. It uses Microlouver technology to limit viewing angles to 60 degrees (30 degrees from center), ensuring information stays visible only to the person directly in front of the display. Whether you're working on confidential files or navigating secure systems, this TAA-compliant solution helps safeguard your screen and your compliance.

No tools. No hassle. The hanging design lets you mount or remove the filter in seconds. Silicone bumpers keep it securely in place while protecting your monitor from scratches.

Purpose-built for widescreen 32-inch 16:9 monitors, this filter delivers more than just privacy. The high-gloss surface keeps colors vibrant, while the fingerprint- and scratch-resistant coating stands up to daily professional use.

By filtering out blue light in the 380-480 nm range, this privacy screen helps reduce eye strain during long sessions in front of the screen. It maintains 65% light transmittance for clear, readable display quality without compromising on comfort.

## Certifications, Reports and Compatibility



## Applications

## Features

- **Protect Sensitive Information**: This TAA-compliant privacy filter uses Microlouver technology to narrow the viewing angle to +/- 30 degrees, shielding 32in 16:9 monitors from visual eavesdropping in offices, hoteling stations or shared spaces
- **Mount and Remove in Seconds**: Quickly attach or remove the hanging privacy filter without tools using its unique mounting design; Included silicone bumpers hold the screen in place and prevent the acrylic frame from contacting the display surface
- **Fits Common 32Inch Widescreen Displays**: Designed for up to 32inch 16:9 monitors, this privacy screen features a highgloss finish to maintain color vibrancy, plus scratch and fingerprintresistant coating for daily professional use
- **Reduce Eye Strain During Extended Use**: Improve visual comfort during long work sessions by blocking blue light in the 380-480 nm range; 65% light transmittance helps maintain screen brightness and readability while reducing eye fatigue
- **The IT Pro's Choice**: Our high-quality privacy screens are trusted across industries and designed to fit nearly every device type, screen size, aspect ratio, and mounting style; Backed by free lifetime 24/5 multi-lingual technical assistance

---

#### Hardware

Warranty	2 Years
Orientation	Horizontal
Mounting Options	Top of Monitor
Aspect Ratio	16:9

---

#### Performance

Minimum Display Size	32"
Maximum Display Size	32"
Fits Curved Display	No
Fits UltraWide Displays	No

---

#### Physical Characteristics

Color	Black
Material	Acrylic
Product Length	21.5 in [54.7 cm]
Product Width	12.6 in [32.0 cm]

Product Height	0.9 in [2.3 cm]
Weight of Product	1.2 lb [0.6 kg]

---

**Packaging Information**

Package Length	19.0 in [48.3 cm]
Package Width	31.7 in [80.5 cm]
Package Height	1.6 in [4.0 cm]
Shipping (Package) Weight	3.8 lb [1.7 kg]

---

***\*Product appearance and specifications are subject to change without notice.***