




**Part Number :** [395005006](#)

**Product Description :** 3.50mm Pitch Eurostyle  
Horizontal Plug, Green Housing, 6 Circuits

**Series Number :** 39500

**Status :** Active

**Product Category :** Terminal Blocks and Barrier  
Strip



---

## Documents and Resources

### Drawings

[395005006\\_sd.pdf](#)

### 3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

### Specifications

[PS-39500-001-001.pdf](#)

---

## Product Environment Compliance

### Compliance

|                    |                                                                                                         |
|--------------------|---------------------------------------------------------------------------------------------------------|
| GADSL/IMDS         | Not Relevant                                                                                            |
| China RoHS         |  per SJ/T 11365-2006 |
| EU ELV             | Not Relevant                                                                                            |
| Low-Halogen Status | Low-Halogen per IEC 61249-2-21                                                                          |
| REACH SVHC         | Contains Lead per D(2025)6375-DC (05 Nov 2025)                                                          |
| EU RoHS            | Compliant with Exemption 6(c) per EU 2015/863                                                           |

### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

## Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

## Substances of Interest

- PFAS

## EU RoHS Certificate of Compliance

## Additional Product Compliance Information

---

# Part Details

## General

|                |                                                                         |
|----------------|-------------------------------------------------------------------------|
| Status         | Active                                                                  |
| Category       | Terminal Blocks and Barrier Strip                                       |
| Series         | 39500                                                                   |
| Description    | 3.50mm Pitch Eurostyle<br>Horizontal Plug, Green Housing, 6<br>Circuits |
| Application    | Wire-to-Board                                                           |
| Component Type | Plug                                                                    |
| Product Name   | Eurostyle Pluggable                                                     |
| Type           | PCB Terminal Blocks and<br>Connectors                                   |
| UPC            | 822350427272                                                            |

## Agency

|    |        |
|----|--------|
| UL | E48521 |
|----|--------|

## Electrical

|                               |      |
|-------------------------------|------|
| Current - Maximum per Contact | 8.0A |
| Voltage - Maximum             | 300V |

## Physical

|                    |       |
|--------------------|-------|
| Circuits (Loaded)  | 6     |
| Circuits (maximum) | 6     |
| Color - Resin      | Green |

|                               |                        |
|-------------------------------|------------------------|
| Entry Angle                   | Vertical               |
| Lock to Mating Part           | None                   |
| Net Weight                    | 4.690/g                |
| Number of Rows                | 1                      |
| Orientation                   | N/A                    |
| Panel Mount                   | No                     |
| PCB Retention                 | N/A                    |
| Pitch - Mating Interface      | 3.50mm                 |
| Pitch - Termination Interface | 3.50mm                 |
| Polarized to Mating Part      | Yes                    |
| Stackable                     | No                     |
| Temperature Range - Operating | -40° to +105°C         |
| Wire Size (AWG)               | 16, 18, 20, 22, 24, 30 |
| Wire Size mm <sup>2</sup>     | 0.05-1.50              |

---

## Mates With / Use With

### Mates with Part(s)

| Description                                   | Part Number                                     |
|-----------------------------------------------|-------------------------------------------------|
| 3.50mm Pitch Eurostyle Vertical PCB Headers   | <a href="#"><u>39501</u></a>                    |
| 3.50mm Pitch Eurostyle Horizontal PCB Headers | <a href="#"><u>39502</u></a>                    |
| Mates With                                    | Most 3.50mm Pitch Industry Standard PCB Headers |