



EAN:	4013288233301	Size:	284x98x45 mm
Part number:	05020340001	Weight:	689 g
Article number:	6006 Joker 2 Set 1	Country of origin:	CZ
		Customs tariff number:	82041200

- Self-setting double spanners
- For hexagon screw heads and bolts with wrench sizes 7,0; 8,0; 9,0; 10,0; 11,0; 12,0; 13,0; 14,0; 15,0; 16,0; 17,0; 18,0; 19,0 (metric)
- For hexagon screw heads and bolts with wrench sizes 1/4"; 5/16"; 3/8"; 7/16"; 1/2"; 17/32"; 9/16"; 19/32"; 5/8"; 11/16"; 3/4" (imperial)
- Automatically and continuously gripping hexagon screws and bolts
- Lever mechanism upon gripping prevents slipping and damage
- With mechanical ratchet functionality for fast and consistent screwdriving without removing the spanner
- Return angle of only 30° when using the corner-width rectangular prisms in the jaw
- In a robust folding pouch with Wera 2go compatibility

2-piece set. Self-setting double spanners for hexagon screw heads and bolts with wrench sizes 7,0; 8,0; 9,0; 10,0; 11,0; 12,0; 13,0 (metric) resp. 1/4"; 5/16"; 3/8"; 7/16"; 1/2" (imperial) and 13,0; 14,0; 15,0; 16,0; 17,0; 18,0; 19,0 (metric) resp. 1/2"; 17/32"; 9/16"; 19/32"; 5/8"; 11/16"; 3/4" (imperial). With its continuous and parallel jaws, the tool replaces several single spanner sizes. The required size is automatically and continuously set when attaching the tool to the hexagon bolt or screw. The integrated lever mechanism securely clamps the hexagon screw or bolt between the jaws, which significantly reduces the risk of slippage or damage. The ratchet feature ensures fast and consistent screwdriving without removing the tool. By using the corner-width rectangular prisms, a return angle of only 30° can be achieved. Ratchet feature and corner-width prism make it possible to work even in confined spaces. The adjustable Joker 6006 double spanner with ratchet functionality is the universal screwdriving tool. Self-setting. Gripping. Spanning. In a robust pouch.


Web link

<https://www.wera.de/en/05020340001>

Wera - 6006 Joker 2 Set 1
05020340001 - 4013288233301


Wera Werkzeuge GmbH
Korzter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de

Joker 6006: automatically and continuously self-setting



With its automatically and continuously gripping parallel jaws, the Joker 6006 double spanner covers all dimensions within the potential operative range. The tool finds the required size by itself when attaching it to the bolt or screw.

Joker 6006: gentle to the screw




The parallel, smooth jaws of the Joker 6006 double spanner offer a seating stress and can thus prevent the nut or screw head from rounding, which can occur when power is transmitted over corners.

Joker 6006: ratchet mechanism for quick working



The ratchet functionality in both jaws of the double spanner ensures fast and consistent screwdriving without removing the tool.

Joker 6006: low return angle



Thanks to the corner-width rectangular prisms in both jaws of the double spanner, a return angle of only 30° can be achieved.

Web link

<https://www.wera.de/en/05020340001>

Wera - 6006 Joker 2 Set 1
05020340001 - 4013288233301

Wera Werkzeuge GmbH
Korzter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de

Set contents:

6006 Joker XS/S Self-setting double spanner, 7; 8; 9; 10 x 1/4; 5/16; 3/8" x 10; 11; 12; 13 x 7/16; 1/2" x 161 mm

05020330001

1x 7; 8; 9; 10 x 1/4; 5/16; 3/8" x 10; 11; 12; 13 x 7/16; 1/2" x 161 mm



6006 Joker M/L Self-setting double spanner, 13; 14; 15; 16 x 1/2; 17/32; 9/16; 19/32; 5/8" x 16; 17; 18; 19 x 5/8; 11/16; 3/4" x 239.4 mm

05020331001

1x 13; 14; 15; 16 x 1/2; 17/32; 9/16; 19/32; 5/8" x 16; 17; 18; 19 x 5/8; 11/16; 3/4" x 239.4 mm



Web link

<https://www.wera.de/en/05020340001>

Wera - 6006 Joker 2 Set 1
05020340001 - 4013288233301

Wera Werkzeuge GmbH
Korzter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de