

Nylon & Stainless Steel Cable Ties



Description

A wide range of Cable Ties are available in Tower's Installation Materials range.

A wide selection of sizes are available as well as natural or black coloured nylon cable ties. Self adhesive bases can be used to secure lighter bundles of cabling, while cradles can be used to secure heavier bundles using screwed fixings.

Tower's newly established 18th Edition Fire Rated range has been created with safety in mind to protect cables from premature collapse in the event of a fire, providing reliable, long-lasting protection in accordance with the IET Wiring Regulations.

Features

Nylon Cable Ties

- Manufactured from Nylon 6.6, compliant to EN 62275 and have good resistance to bases, oils, greases, oil derivatives and chloride solvents. Limited resistance to acids and no resistance to phenols.
- Flammability of raw material: UL 94 - V2
- Black ties have enhanced UV resistance.

Stainless Steel Cable Ties

- Manufactured from 316 Stainless Steel for the most corrosive environments
- Complies with BS 7671 18th Edition regulations for fire safety.
- Operating Temperature of -80°C to + 538°C.

Standards

- BS 7671 Requirements for Electrical Installations
- EN 62275 Cable Management Systems – Cable Ties for Electrical Installations

Range

Nylon 6/6 Cable Ties (Bags of 100)

2.5x100mm Nylon Cable Tie Black	29CT12BK
2.5x100mm Nylon Cable Tie Natural	29CT12NU
3.6x150mm Nylon Cable Tie Black	29CT22BK
3.6x150mm Nylon Cable Tie Natural	29CT22NU
3.6x200mm Nylon Cable Tie Black	29CT24BK
3.6x200mm Nylon Cable Tie Natural	29CT24NU
4.8x200mm Nylon Cable Tie Black	29CT32BK
4.8x200mm Nylon Cable Tie Natural	29CT32NU
4.8x300mm Nylon Cable Tie Black	29CT34BK
4.8x300mm Nylon Cable Tie Natural	29CT34NU
4.8x370mm Nylon Cable Tie Black	29CT36BK
4.8x370mm Nylon Cable Tie Natural	29CT36NU

Nylon 6/6 Cable Ties (Bags of 100) Cont.

7.6x300mm Nylon Cable Tie Black	29CT44BK
7.6x300mm Nylon Cable Tie Natural	29CT44NU
7.6x380mm Nylon Cable Tie Black	29CT46BK
7.6x380mm Nylon Cable Tie Natural	29CT46NU
8.8x780mm Nylon Cable Tie Black	29CT56BK
8.8x780mm Nylon Cable Tie Natural	29CT56NU

316 Stainless Steel Roller Ball Cable Ties (Bags of 100)

4.6x150mm 316 Stainless Steel Cable Tie	29CT80SS
4.6x200mm 316 Stainless Steel Cable Tie	29CT81SS
4.6x300mm 316 Stainless Steel Cable Tie	29CT83SS
4.6x360mm 316 Stainless Steel Cable Tie	29CT84SS
4.6x520mm 316 Stainless Steel Cable Tie	29CT85SS
7.9x300mm 316 Stainless Steel Cable Tie	29CT88SS
7.9x360mm 316 Stainless Steel Cable Tie	29CT89SS
7.9x520mm 316 Stainless Steel Cable Tie	29CT90SS
7.9x840mm 316 Stainless Steel Cable Tie	29CT92SS

316 Stainless Steel Roller Ball Cable Ties (Bags of 50)

7.9x520mm 316 Stainless Steel Cable Tie	29CTM4SS
7.9x840mm 316 Stainless Steel Cable Tie	29CTM6SS

Self-Adhesive Bases (Bags of 100)

19x19mm Nylon Adhesive Base Black	29CT71BK
19x19mm Nylon Adhesive Base Natural	29CT71NU
28x28mm Nylon Adhesive Base Black	29CT73BK
28x28mm Nylon Adhesive Base Natural	29CT73NU

316 Stainless Steel Cable Tie Mounts (Bags of 100)

Stainless Steel Cable Tie Mount M4	29CTM4SS
Stainless Steel Cable Tie Mount M6	29CTM6SS

Screw Mounted Cradles (Bags of 100)

22x16mm Nylon Cradle Black	29CT75BK
22x16mm Nylon Cradle Natural	29CT75NU