




# JWPFF CONNECTOR



2.0mm/Wire-to-Wire Connectors (Waterproof Type)



## Part Number:

- AJWPFJWPF22K51TR

## Description:

- JST Series – [JWPF Series](#)
- Pitch – 2mm
- Cable length (inside dimension) – 51mm

## Material Specification:

- (1) Terminal: SWPT-001T-P025
- (2) Terminal: SWPR-001T-P025
- (3) Cable Type: UL1007
- (3) Cable Size: 22AWG
- (3) Cable Colour: BLACK

## Applicable Housings:

| No. of Circuits | Part Number     | Housing Type | Rows   |
|-----------------|-----------------|--------------|--------|
| 2               | 02T-JWPF-VSLE-S | Tab          | Single |
| 3               | 03T-JWPF-VSLE-S | Tab          | Single |
| 4               | 04T-JWPF-VSLE-S | Tab          | Single |
| 6               | 06T-JWPF-VSLE-D | Tab          | Dual   |
| 8               | 08T-JWPF-VSLE-D | Tab          | Dual   |
| 2               | 02R-JWPF-VSLE-S | Receptacle   | Single |
| 3               | 03R-JWPF-VSLE-S | Receptacle   | Single |
| 4               | 04R-JWPF-VSLE-S | Receptacle   | Single |
| 6               | 06R-JWPF-VSLE-D | Receptacle   | Dual   |
| 8               | 08R-JWPF-VSLE-D | Receptacle   | Dual   |

## Accessories:

- Extraction Tool: EJ-JWPF

## Quality

- We trust and believe in our product. Each step of our development and manufacturing process is focused on delivering a fault-free product. JST does not compromise on quality.

## Additional Information:


Alternative colour and length cables are available upon request, please contact JST for further details by e-mailing [jukma@jst.co.uk](mailto:jukma@jst.co.uk)



# JWPF CONNECTOR

**JST**  
The Quality Connection

2.0mm/Wire-to-Wire Connectors (Waterproof Type)



A JWPF JWPF 22 K 51 TR

**Supply Form:** Assembled Wire

**Terminal Series End A:** JWPF Connector

**Terminal Series End B:** JWPF Connector

**Cable Size:** 22awg (??AWG)

**Cable Colour:** B (Blue), K (Black), R (Red), N (Brown), H (Grey)  
O (Orange), Y (Yellow), W (White), M (Green), P (Purple), PK (Pink)

**Cable Length:** 51mm (????mm)

**Contact Type:** T (Tab – SWPT-001T-P025),  
R (Receptacle – SWPR-001T-P025)  
TR (Tab to Receptacle)

## Additional Information:

Alternative colour and length cables are available upon request, please contact JST for further details by e-mailing [jukma@jst.co.uk](mailto:jukma@jst.co.uk)