

Wireless USB-C to HDMI Extender for Meeting Rooms and Huddle Spaces, 4K 60Hz, 65ft Range, USB Powered, Plug-and-Play Transmitter and Receiver Kit

Product ID: 4KUSBC-WIRELESS-65FT




Extend a USB-C device to an HDMI display wirelessly at 4K 60Hz with a driverless kit that removes cabling limits and simplifies AV deployments.

Pre-paired transmitter and receiver deliver 4K 60Hz video without network access, drivers, software, reducing install time in boardrooms, digital signage, and restricted networks. Skip cable runs and avoid infrastructure changes while maintaining reliable signal performance.

Driverless operation supports any Windows, macOS, and ChromeOS laptop, enabling consistent extension across varied devices. No software or network dependency means fewer compatibility issues and less IT overhead when deploying across multiple meeting spaces.

Compact, plug-and-play design lets users present immediately, ideal for huddle spaces and trade shows. The transmitter is powered via the hosts USB-C connection, while the receiver draw power from a USB port on the display or nearby wall charger, removing external adapters and simplifying placement for clean, efficient setups.

Certifications, Reports and Compatibility



Applications

- Stream video from your laptop to a wall-mounted TV without running cables across the room
- Enable clean, clutter-free conference room setups by wirelessly connecting presentation devices to a projector or display

Features

- **Wireless 4K 60Hz Without Infrastructure Constraints**: Extend a USB-C device to an HDMI display at 4K 60Hz using a pre-paired kit that requires no drivers, reducing setup time and eliminating cabling challenges in complex AV or network-restricted environments
- **Standardize Video Extension Across Meeting Spaces**: Driverless, software-free solution with no network connection required works with any HDMI device, including Windows, macOS, and ChromeOS laptops, enabling reliable HDMI extension across mixed devices
- **Deploy with Zero Training Required**: Compact, plug-and-play design allows non-technical users to install and present instantly in meeting rooms, huddle spaces, and trade shows, eliminating cable runs, reducing setup time, and avoiding support tickets
- **Eliminate Power Clutter Across Installations**: The USB-C transmitter draws power from the host while the receiver can be powered via a USB port on the display or a wall charger, removing bulky adapters and simplifying AV deployments across meeting rooms
- **The IT Pro's Choice**: Work with a single trusted partner for all your A/V connectivity needs, backed by decades of expertise from legacy VGA to modern USB4 and AVoIP solutions, plus free lifetime 24/5 multilingual technical assistance

Hardware

Warranty	2 Years
Ports	1
Cabling	Wireless Ethernet
Audio	Yes
Rack-Mountable	No
Chipset ID	Transmitter: VCT6601 Receiver: VCT6602
Daisy-Chain	No

Performance

Max Distance	66ft [20m]
Frequency	5GHz

General Specifications		Latency: 100ms ~ 250ms
Connector(s)	Local Unit Connectors	1 - USB-C (DP Alt-Mode)
	Remote Unit Connectors	1 - HDMI
Software		
	OS Compatibility	No Drivers or Software Required
Special Notes / Requirements		
	Note	Transmission distances may vary based on the installation environment. Solid structures like walls, bricks, and glass can reduce or completely block signals.
Indicators		
	LED Indicators	1 - Power LED: Solid Red - The device is receiving power 1 - Signal LED: Solid - The unit is successfully connected Slow Flash - Waiting for connection Quick Flash - The unit is in pairing mode 1 - Video LED: Off - No input video signal detected Solid - Video input signal detected Quick Flash - Restoring to factory defaults
Power		
	Power Source	USB-Powered
	Power Consumption (In Watts)	Transmitter: < 5W Receiver: < 3.5W
Environmental		
	Operating Temperature	-20C to 50C (-4F to 122F)
	Storage Temperature	-30C to 70C (-22F to 158F)

Humidity 0% ~ 90% RH

Physical Characteristics

Color	Space Gray
Material	ABS
Cable Length	4.7 in [12 cm]
Product Length	9.1 in [230 mm]
Product Width	1.6 in [40 mm]
Product Height	0.6 in [15 mm]
Weight of Product	4.0 oz [112 g]

Packaging Information

Package Length	5.9 in [14.9 cm]
Package Width	7.8 in [19.9 cm]
Package Height	3.1 in [8.0 cm]
Shipping (Package) Weight	12.0 oz [340.0 g]

What's in the Box

Included in Package	1 - USB-C Transmitter
	1 - HDMI Receiver
	2 - USB Power Cable
	1 - Product Documentation

Warranty Information

Warranty	2 Years
----------	---------

**Product appearance and specifications are subject to change without notice.*