

Set

**PMS SKS safety**



4 mm safety system

| Product           | PMS SKS safety                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                         |
|-------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| description       | <p>Safety test equipment set</p> <ul style="list-style-type: none"> <li>- KLEPS 2600<br/>Clamp-type test probe with rotating grip jaws and flexible shaft for clamping of pins and wires up to <math>\varnothing</math> 4 mm.</li> <li>- PRUEF 2600<br/>Test probe with slender stainless steel tip for penetration of oxide layers.</li> <li>- AK 2 B<br/>Contact-protected alligator clip for clamping of finest wires, clamping range up to a maximum of 9.5 mm bolt diameter.</li> <li>- MLS WS 50/1<br/>Safety test lead with 4 mm safety plugs on both sides and onward connection capability (length: 50 cm)</li> <li>- MLS WS 100/1<br/>Safety test lead with 4 mm safety plugs on both sides and onward connection capability (length: 100 cm)</li> <li>- MLS WS 200/1<br/>Safety test lead with 4 mm safety plugs on both sides and onward connection capability (length: 200 cm)</li> </ul> <p>Please find further technical details on individual product data sheets.</p> |
| Articlenumber     | 932795001                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                              |
| technical data    |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                        |
| scope of delivery | <p>           1 x measuring lead MLS WS 50/1 black (934 068-100)<br/>           1 x measuring lead MLS WS 50/1 red (934 068-101)<br/>           2 x measuring lead MLS WS 100/1 black (934 095-100)<br/>           2 x measuring lead MLS WS 100/1 red (934 095-101)<br/>           1 x measuring lead MLS WS 200/1 black (934 069-100)<br/>           1 x measuring lead MLS WS 200/1 red (934 069-101)<br/>           1 x clamp-type test probe KLEPS 2600 black (972 306-100)<br/>           1 x clamp-type test probe KLEPS 2600 red (972 306-101)<br/>           1 x alligator clip AK 2 B black (932 435-100)<br/>           1 x alligator clip AK 2 B red (932 435-101)<br/>           1 x test probe PRUEF 2600 black (972 317-100)<br/>           1 x test probe PRUEF 2600 red (972 317-101)         </p>                                                                                                                                                                    |

stand : November 13, 2025 5:59 PM