

20mm Round Rocker Switches **multicomp**PRO

**RoHS
Compliant**



MP004431



MP004432
MP004433
MP005722



MP004434
MP004435
MP005723



MP004436
MP004438
MP005724



MP004437
MP005725



MP005718



MP005719



MP005720



MP005721




MP005726



MP005727

Features


Housing Material	: Nylon #66 UL 94V-2
Rocker Material	: Nylon #66 UL 94V-2
Terminal Material	: Copper alloy SN or AG plated
Contact Material	: AgNi (15) alloy



Specification

- 20mm Round Rocker Switch
- SPDT Centre off
- UL, ENEC Approvals

Cut Out		
Z	Y	X
0.75-1.25	20.8	20.2
1.25-2	20.8	20.4
2-3	20.8	20.6



Specifications Table

Part Number	Rating	Actuator Colour	Body Colour	Marking	Switch Action	Illumination Type	
MP004431	6A / 250V AC	Black	Black	I O I	SP Centre-off Latching	Non-illuminated	
MP004432	10A / 12V DC	Red		-		SPST Latching	Illuminated
MP004433	10A / 24V DC						
MP004434	10A / 12V DC	Green					
MP004435	10A / 24V DC						
MP004436	10(4)A / 250V AC	Black	Black			SPDT Changeover	Non-Illuminated
MP004437	6A / 250V AC	White	White	SPST Momentary			
MP004438	10A / 250V AC	Black	Black	SPDT centre-off Momentary Both sides			
MP005718	6A / 250V AC			O I	SPST latching		

Newark.com/multicomp-pro
Farnell.com/multicomp-pro
sg.element14.com/b/multicomp-pro

multicompPRO



20mm Round Rocker Switches **multicomp**PRO

Part Number	Rating	Actuator Colour	Body Colour	Marking	Switch Action	Illumination Type
MP005719	6A / 250V AC	Black	Black	-	SPST Momentary	Non-Illuminated
MP005720				0 I	DPDT Latching	
MP005721		Red		-	SPST Latching	Illuminated Red Dot
MP005722						
MP005723		Green				
MP005724		Black				
MP005725		White	White			
MP005726	6(2)A 250V AC T125/55 1E4 16A 125V AC	Black	Black	-	SPDT centre-off Latching	Non-Illuminated
MP005727	6(2)A 250V AC T125/55 1E4 10A 125V AC	White	White	-	SP On-off Latching	

Rocker Switch Cap



MP004439



Specification

- Splash proof cap to fit over 20mm round rocker switches

Dimensions : Millimetres

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro
Farnell.com/multicomp-pro
sg.element14.com/b/multicomp-pro

multicompPRO