


2m (6ft) Laptop Power Cord, EU Schuko to C5, 2.5A 250V, 18AWG, Notebook / Laptop Replacement AC Cord, Power Brick Cord, Laptop Charger Cable, Clover Leaf/Mickey Mouse Power Cord

Product ID: PXTNB3SEU2M



The PXTNB3SEU2M 3-Slot Laptop Power Cord features one EU power plug and one 3-prong connector, making it a suitable replacement cable for an HP, Toshiba or any other laptop that features a cloverleaf/C5 power connection.

Designed for durability and dependability, this Cloverleaf Power Cord is backed by our Lifetime Warranty.

Certifications, Reports and Compatibility



Applications

- Spare/replacement laptop power cable for use with grounded European/C5 power outlets
- Extend the connection distance between your laptop and power outlet by 2m

Features

- **AC POWER CORD:** This 2m (6.5ft) 18AWG flexible laptop power cord with EU Schuko Plug and IEC 60320 C5 connectors is suitable for workstation/home office use. Rated to carry 250V at 2.5A
- **PERFORMANCE AND SAFETY:** Fully molded strain relief for durability and VDE approved connectors. Fire Rating: VW-1. 3 conductor Notebook Power Cable made from 100% Copper Wire

- **SPECS:** 2m (6.5ft) Power Cable EU Schuko Plug to IEC 60320 C5 18AWG (0.75mm²) 250V 2.5A (Max) Jacket Rating: H05VV-F Jacket Material: PVC Color: Black Temperature Range: -10 to 60 Jacket Dimensions: 0.13x0.26in (3.5x6.8 mm)

- **COMPATIBILITY:** AC Power Cord EU Schuko Plug works with European outlets IEC 60320 C5 connector works with most power bricks for laptops/notebooks, monitors, scanners, printers, and more Replacement laptop power supply cable/cord

- **THE IT PRO'S CHOICE:** Designed and built for IT Professionals, this laptop charger cord is backed for life, including free lifetime 24/5 multi-lingual technical assistance

General

UPC	065030849418
Package Quantity	1
Warranty	Lifetime

Power

Input Voltage	250 AC
Input Current	2.5 A

Physical & Environmental

Color	Black
Wire Gauge	0.75 sq mm
Cable Length	6.6 ft [2 m]
Product Length	6.6 ft [2.0 m]
Product Width	0.9 in [22.0 mm]
Product Height	0.0 in [0.0 mm]
Weight of Product	7.0 oz [197.0 g]

Hardware

Number of Conductors	3
Cable Jacket Material	PVC - Polyvinyl Chloride
Fire Rating	VW-1 Rated

Packaging &

In-the-Box

Included in Package	1 - 2m Laptop Power Cord - 3 Slot for EU
Package Width	3.0 in [75 mm]
Package Depth	10.6 in [26.9 cm]
Package Height	1.7 in [44 mm]
Shipping (Package) Weight	7.3 oz [206 g]

Connector(s)

Connector 1 (Quantity)	1
Connector 1	CEE 7/7 (250V AC, 16A)
Connector 2 (Quantity)	1
Connector 2	IEC C5 (250V AC, 2.5A)

****Product appearance and specifications are subject to change without notice.***