



Focus Wireless Presenter with Red Laser Pointer

PN: 32365

Charge Less, Present More.

The Verbatim Focus Wireless Presenter combines style and performance in a slim aluminium design. Featuring intuitive controls, red laser pointer, 30m wireless range, and rechargeable battery, it ensures seamless presenting. With USB-A/C compatibility across major systems, it's perfect for professionals on the go—reliable, portable, and effortlessly professional.

- Aluminium alloy body with a fine, frosted texture.
- Built-in rechargeable lithium battery, rechargeable via USB-C cable.
- Window task switching function.
- Plug & play – no drivers or setup required
- Can be used worldwide.
- Works with Windows, macOS, and Android devices
- Red laser pointer with up to 100m wireless range
- Supplied with a travel pouch



Rechargeable
Battery Inside



Easy Slide
Navigation



PN: 32365

Product Specifications

- RF Frequency: 2.4 GHz
- Operating Distance: 30 m
- Laser Class I
- Laser Distance: 80-100 m
- Laser Wavelength: 650 nm, Red pointer
- Laser Output Power: < 0.4 mW
- Lithium-ion polymer battery: 250 mAh 0.925 Wh / 3.7 V
- USB-C Input: 5 V = 1 A
- Operating system: Windows 8/10/11; Mac OS 10.1.2 or above; Android
- Operating Temperature: -10 °C - +45°C
- Storage Temperature: -10 °C - +45°C

Languages

Front of pack: English

Back of pack: English, French, German, Dutch, Italian, Spanish, Portuguese, Polish, Russian, Czech, Hungarian, Croatian, Serbian, Slovakian, Romanian, Turkish, Traditional Chinese, Simplified Chinese, Korean, Japanese

Quick Installation Languages

English, French, German, Traditional Chinese + Support text in English, French, German, Dutch, Italian, Spanish, Portuguese, Polish, Russian, Czech, Hungarian, Croatian, Slovakian, Romanian, Turkish, Traditional Chinese, Simplified Chinese, Korean, Japanese



PN	Material	Battery Capacity	Colour	Pack Content:
32365	PC	250 mAh	Grey/Black	• Verbatim Focus Wireless Presenter with red laser pointer • USB-A receiver • USB-A to USB-C adapter • USB-A to USB-C cable 50 cm • Protective Pouch • Quick start Guide

Focus Wireless Presenter with Red Laser Pointer



Reorder No.	Description	Tariff Code	Barcode	EAN-128	EAN-14
32365	Verbatim Focus Wireless presenter with red laser pointer	84716070	023942323655	(02)00023942323655(37)10(91)862 (02)00023942323655(37)40(91)862	20023942323659 50023942323650

Reorder No.	32366
Product Dimensions L x W x H	116.6 x 38.1 x 25.73 mm
Product Weight	42 g
Units per Pack	1
Pack Dimensions L x W x H	180 x 68 x 36 mm
Pack Weight	95.5 g
Units per Inner Carton	10
Inner Carton Dimensions L x W x H	380 x 200 x 80 mm
Inner Carton Weight	1130 g
Units per Outer Carton	40
Outer Carton Dimensions L x W x H	400 x 220 x 340mm
Outer Cartons Weight	5000 g
Outer Cartons per Layer	13
Layers per Pallet	3
Units per Pallet	1560

