# 20mm Round Rocker Switches

RoHS Compliant



MP004431



MP005722
MP004432



MP004434
MP004435
MP005723



MP004436
MP004438
MP005724



MP004437
MP005725



MP005718



MP005719



MP005720



MP005721




MP005726




MP005727

## Features

| | |
|---|---|
| Housing Material | : Nylon #66 UL 94V-2 |
| Rocker Material | Nylon #66 UL 94V-2 |
| Terminal Material | : Copper alloy SN or AG plated |
| Contact Material | : AgNi (15) alloy |




## Specification

- 20mm Round Rocker Switch
- SPDT Centre off
- UL, ENEC Approvals

Cut Out

| Z | Y | X |
|---|---|---|
| 0.75-1.25 | 20.8 | 20.2 |
| 1.25-2 | 20.8 | 20.4 |
| 2-3 | 20.8 | 20.6 |

## Specifications Table

| Part Number | Rating | Actuator Colour | Body Colour | Marking | Switch Action | Illumination Type |
|---|---|---|---|---|---|---|
| MP004431 | 6A / 250V AC | Black | Black | I O I I | SP Centre-off Latching | Non-illuminated |
| MP004432 | 10A / 12V DC | Red | | - | SPST Latching | Illuminated |
| MP004434 | 10A / 12V DC | Green | | | | |
| MP004435 | 10A / 24V DC | | | | | |
| MP004436 | 10(4)A / 250V AC | Black | Black | | SPDT Changeover | Non-Illuminated |
| MP004437 | 6A / 250V AC | White | White | | SPST Momentary | |
| MP004438 | 10A / 250V AC | Black | Black | | SPDT centre-off Momentary Both sides | |
| MP005718 | 6A / 250V AC | | | O I | SPST latching | |

Newark.com/multicomp-pro
Farnell.com/multicomp-pro
sg.element14.com/b/multicomp-pro


# 20mm Round Rocker Switches

| Part Number | Rating | Actuator Colour | Body Colour | Marking | Switch Action | Illumination Type |
|---|---|---|---|---|---|---|
| MP005719 | 6A / 250V AC | Black | Black | - | SPST Momentary | Non-Illuminated |
| MP005720 | | | | 0 I | DPDT Latching | |
| MP005721 | | Red | | - | SPST Latching | Illuminated Red Dot |
| MP005722 | | | | | | Illuminated |
| MP005723 | | Green | | | | |
| MP005724 | | Black | | | | Non-Illuminated |
| MP005725 | | White | White | | | |
| MP005726 | 6(2)A 250V AC T125/55 1E4 16A 125V AC | Black | Black | - | SPDT centre-off Latching | |
| MP005727 | 6(2)A 250V AC T125/55 1E4 10A 125V AC | White | White | - | SP On-off Latching | |

## Rocker Switch Cap



**MP004439**




## Specification

- Splash proof cap to fit over 20mm round rocker switches

Dimensions : Millimetres

**Important Notice :** This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.