2-port HDMI splitter and signal amplifier - TAA

Product ID: ST122HDMI2

The ST122HDMI2 2-Port High Speed HDMI Splitter and Signal Amplifier lets you share a single HDMI source signal with audio between two HDMI or DVI (using HDMI to DVI adapter - see Accessories) enabled displays simultaneously.

Supporting True HD 1080p video resolutions, the HDMI splitter acts as a distribution amplifier that enables you to situate your HDMI-capable displays up to 50ft (15m) away from the splitter, and features 3.5mm audio connections, giving you the option of sending your accompanying audio signal through the HDMI cable, or through a separate channel.

The HDMI splitter is easy to install and use with no software or configuration required, for a completely plug-and-play setup that can be used with HDMI output devices such as Blu-ray players or desktop/laptop computers.

This product is TAA compliant and backed by a Startech.com 3-year warranty with free lifetime technical support.

Certifications, Reports and Compatibility

Applications

• Connect HDMI enabled projectors, monitors, plasma screens, commercial billboards, and wall display systems

• Ideal for business conference rooms and trade show displays

• Great for digital signage applications displaying video advertisements with audio in retail environments

• Perfect for classrooms and business multimedia presentations

• Display information in waiting rooms or to patients in healthcare facilities

• Financial applications, including stock tickers or promotion of new products/services

Features

• 2-PORT HDMI SPLITTER: Displays the same image with sound on 2 screens; HDMI splitter with signal amplifier splits an HDMI source into two Full HD 1080p video signals with no loss of quality

• EDID EMULATION: 1x2 HDMI splitter automatically passes EDID between your video source and the display attached to port 1 ensuring native settings (such as resolution and refresh rate) are configured

• AUDIO SUPPORT: Audio output is supported on all ports simultaneously; Supports HDMI audio or 3.5mm stereo audio connection, allowing you to send your accompanying audio signal through the HDMI cable, or through a separate channel

• EASY SETUP: Reach up to 49ft (15m) with this HDMI splitter with signal amplifier; Simply connect the cables and power to start using; Wide screen monitor formats supported; TAA Compliant

• THE IT PRO'S CHOICE: Designed and built for IT Professionals, this HDMI Splitter with rugged steel enclosure is backed for two years, including free lifetime 24/5 multi-lingual technical assistance

General		
	UPC	065030842457
	Package Quantity	1
	Warranty	2 Years
Power		
	Power Source	AC Adapter Included
	Input Voltage	100 - 240 AC
	Input Current	0.6A
	Output Voltage	12V DC
	Output Current	1.5
	Center Tip Polarity	Positive
	Plug Type	M
	Power Consumption	13

Physical & Environmental		
	Color	Black
	Material	Steel
	Product Length	7.1 in [18.0 cm]
	Product Width	3.1 in [80.0 mm]
	Product Height	0.8 in [20.0 mm]
	Weight of Product	13.4 oz [380.0 g]
	Operating Temperature	0C to 40C (32F to 104F)
	Storage Temperature	-20C to 60C (-4F to 140F)
	Humidity	0~80% RH
Performance		
	Maximum Cable Length	49.2 ft [15 m]
	Maximum Digital Resolutions	HDTV 1080p PC Resolution 1920x1200
	Wide Screen Supported	Yes
Hardware		
	AV Input	HDMI
	Number of Ports	2
	AV Output	HDMI
	Audio	Yes
	LED Indicators	3 - Port Power/Input - Green indicates connection, Blue indicates activity
Packaging & In-the-Box		
	Included in Package	1 - HDMI splitter 1 - universal power adapter (NA / EU / UK / AU) 1 - instruction manual
	Package Width	8.7 in [22 cm]

	Package Depth	4.0 in [10.2 cm]
	Package Height	3.7 in [94 mm]
	Shipping (Package) Weight	24.9 oz [704 g]

Connector(s)		
	Connector 1 (Quantity)	1
	Connector 1	HDMI
	Connector 2 (Quantity)	1
	Connector 2	3.5mm (3 Conductors, TRS)
	Connector 3 (Quantity)	2
	Connector 3	HDMI
	Connector 4 (Quantity)	2
	Connector 4	3.5mm (3 Conductors, TRS)

Product appearance and specifications are subject to change without notice.