15ft (4.6m) DisplayPort to VGA Cable - Active DisplayPort to VGA Adapter Cable - 1080p Video - DP to VGA Monitor Cable - DP 1.2 to VGA Converter - Latching DP Connector

Product ID: DP2VGAMM15B

The DP2VGAMM15B 15ft active DisplayPort to VGA converter cable lets you connect your DisplayPort-equipped desktop or laptop directly to a VGA monitor or projector at a longer distance than a standard-length cable would support, while saving the expense of additional adapters.

Plus, because the converter cable supports video resolutions up to 1920x1200 you can convert a DisplayPort video source to VGA without sacrificing video quality.

The DP2VGAMM15B is backed by a 3-year StarTech.com warranty and free lifetime technical support.

Certifications, Reports and Compatibility

Applications

• Connect your existing VGA display device (monitor, projector) to a DisplayPort output device (Desktop, Laptop computer)

• Use your VGA monitor as a secondary display, connected to a DisplayPort output

• Connect a DisplayPort computer to a VGA projector for presentations or meetings in a boardroom or auditorium setting

Features

• DISPLAYPORT TO VGA CABLE: 15ft (4.6m) DisplayPort 1.2 (HBR2) adapter cable lets you connect a single VGA display supporting 2048x1280, 1920x1200 & 1920x1080 (1080p) at 60Hz; EDID & DDC pass-through ensure compatibility between source & display

• COMPATIBILITY: Active digital to analog converter supports DP or DP++ source w/ standard DP connector incl workstations, desktops (AMD/Nvidia), laptops, small form factor computers & docking stations

• INTEGRATED DISPLAY CABLE: Adapter cable has slim & flexible design w/ adapter chip built into VGA connector reducing clutter & providing a tidy install in the office, boardroom or home office; 15' length supports longer distance than traditional VGA cable

• LATCHING DISPLAYPORT & SCREW LOCKING VGA: Latching DP connector ensures a solid host connection, and chip built into VGA connector minimizes signal loss Supports VGA screw locking cable to prevent cable from coming loose or accidental disconnection

• EASY TO USE: With no software or drivers required, the DP to VGA video converter cable/cord works with any OS including macOS, Windows & Ubuntu DP Source to VGA Monitor/Display/Projector DisplayPort Male to VGA Male Cable

General		
	UPC	065030852487
	Package Quantity	1
	Warranty	3 Years
Physical & Environmental		
	Color	Black
	Cable Length	15.0 ft [4.6 m]
	Product Length	15.0 ft [4.6 m]
	Product Width	1.6 in [40 mm]
	Product Height	0.6 in [15 mm]
	Weight of Product	7.7 oz [218 g]
	Operating Temperature	0C to 60C (32F to 140F)
	Storage Temperature	-10C to 70C (14F to 158F)
	Humidity	40%-85%RH
Performance		

	HDR Support	No
	Maximum Cable Length	15.0 ft [4.6 m]
	MTBF	1,449,804 hours
	Audio Specifications	VGA - No Audio Support
	Maximum Analog Resolutions	1920x1200 / 1080p (Output)
	Maximum Digital Resolutions	1920x1200 / 1080p (Input)
Hardware		
	Active or Passive Adapter	Active
	AV Input	DisplayPort - 1.2
	AV Output	VGA
	Audio	No
	Number of Displays	1
	Chipset ID	Analogix - 9832
Packaging & In-the-Box		
	Included in Package	1 - DisplayPort to VGA Adapter Cable
	Package Width	6.0 in [15.2 cm]
	Package Depth	7.7 in [19.5 cm]
	Package Height	1.4 in [36 mm]
	Shipping (Package) Weight	8.6 oz [244 g]
Connector(s)		
	Connector 1 (Quantity)	1
	Connector 1	DisplayPort
	Connector 2 (Quantity)	1
	Connector 2	VGA

Product appearance and specifications are subject to change without notice.