4-Port USB-A Hub, 5Gbps, Bus Powered, USB-A to 4x USB-A Mini Hub, Extra Long 2ft/61cm Host Cable, PCR Plastic, Portable Desktop / Laptop USB Hub

Product ID: H5A4A-USB-HUB-2



Add up to four USB 3.0 devices to your laptop or PC using a single USB-A port.

This lightweight 4-port hub is built for portability with a small footprint, 2ft (61cm) built-in cable, and no need for an external power adapter. Ideal for shared workspaces, home offices, and travel.

With three ports on one side and one on the end, this hub makes it easy to plug and unplug devices when space is tight.

OS-independent and driver-free, this hub works with Windows, macOS, ChromeOS, and Linux. Just connect and start using.

This hub features a housing made from 70% post-consumer recycled (PCR) plastic and a cable jacket composed of 35% PCR TPE (Thermoplastic Elastomer). The product also ships in FSC Mix packaging made from responsibly sourced materials. These materials help align your IT infrastructure with your organization's sustainability goals, without compromising on quality or durability.

StarTech.com Connectivity Tools offer practical utilities to support device management and increase productivity in modern IT environments. The applicable software for this product is the USB Event Monitoring Utility which allows administrators to track and log connected USB devices.

Visit StarTech.com/Connectivity-Tools to download the Enterprise Management Tools.

Certifications, Reports and Compatibility



Applications

• Compatible with USB Type-A host devices incl. Lenovo X1 Carbon, Dell XPS and Microsoft Surface

• Make hard to access USB ports more accessible, by being able to position the hub anywhere the cable will reach

• Separate tightly packed USB ports, to better accommodate larger USB plugs or prevent overcrowding

Features

• Expand Your USB Connectivity: Add four 5Gbps USB-A ports to a USB-A laptop or desktop with limited connectivity, allowing you to connect keyboards, mice, flash drives, and card readers; Ideal for office and remote work, classrooms, hot-desking, and travel

• Extra-Long Cable: Compact design with a built-in 2ft (61cm) cable for extended reach and reduced USB-A connector strain on 2-in-1 devices; Hook and loop tie for tangle-free storage and three ports on one side and one on the end for clean, easy access

• No Power Adapter Required: Versatile USB-A hub is bus-powered, drawing power directly from a computer's USB-A port, removing the need for an external power adapter; Overcurrent Protection (OCP) protects connected peripherals from overdrawing power

• Plug-and-Play: This OS-independent / driverless USB-A hub supports Windows, macOS, Linux, and ChromeOS and configures automatically when connected to a host; Compatible with USB Type-A host devices incl. Lenovo X1 Carbon, Dell XPS and Microsoft Surface

• The IT Pro's Sustainable Choice: Built with 70% post-consumer recycled plastic, a 35% PCR TPE cable jacket, and FSC Mix packaging from responsibly sourced materials, this USB hub minimizes environmental impact while delivering enterprise-grade performance

General		
	UPC	065030923903
	Warranty	2 Years
Special Notes / Requirements		
	System and Cable Requirements	Available USB Port
Power		
	Power Source	USB-Powered
Physical & Environmental		

	Color	Black
	Material	70% PCR Plastic
	Cable Length	2.4 in [61 mm]
	Product Length	3.8 in [95.5 mm]
	Product Width	1.3 in [31.8 mm]
	Product Height	0.5 in [11.5 mm]
	Weight of Product	1.6 oz [44 g]
	Operating Temperature	0C to 40C (32F to 104F)
	Storage Temperature	-20C to 60C (-4F to 140F)
	Humidity	90%RH Max
Performance		
	Maximum Data Transfer Rate	5 Gbps (USB 3.2 Gen 1)
	Type and Rate	USB 5Gbps
	UASP Support	Yes
	MTBF	196439 hours
Hardware		
	USB-C Device Port(s)	No
	USB-C Host Connection	No
	Fast-Charge Port(s)	No
	Number of Ports	4
	Cable Jacket Material	35% PCR TPE - Thermoplastic Elastomers
	Interface	USB 3.2 Gen 1 (5Gbps)
	Bus Type	USB 3.2 Gen 1 (5Gbps)
	Chipset ID	VIA - VL817S
	Form Factor	Compact

Packaging & In-the-Box		
	Included in Package	1 - USB Hub
		1 - Cable Tie
		1 - Product Documentation
	Package Width	3.9 in [100 mm]
	Package Depth	6.7 in [17 cm]
	Package Height	1.2 in [30 mm]
	Shipping (Package) Weight	3.7 oz [106 g]
Connector(s)		
	Host Connector 1 (Quantity)	1
	Host Connector 1	USB-A (5Gbps, 4.5W)
	Connector 1 (Quantity)	4
	Connector 1	USB-A (5Gbps, 4.5W)

Product appearance and specifications are subject to change without notice.