

# PRO-TORCH™ PT-220




**GAS FILLING**



**PIEZO IGNITION**



**KILL OFF SWITCH**



[www.pro-iroda.com.tw](http://www.pro-iroda.com.tw)

## FEATURES:

- 220 MIN. REFILLABLE BUTANE GAS TANK.
- ADJUSTABLE AIR FLOW CONTROL VALVE.
- ADJUSTABLE GAS FLOW CONTROL VALVE.
- SAFETY LOCKING IGNITION BUTTON.
- SAFETY KILL/OFF SWITCH.
- CONVENIENT, LIGHTWEIGHT, YET STURDY DESIGN.
- BRASS BODY COVERED WITH PROTECTIVE GRIP.
- STURDY REMOVABLE BASE FOR ADDED SAFETY.

## WARNING:

- DO NOT TOUCH FLAME GUARD WHILE IN USE OR UNTIL SUFFICIENT TIME HAS PASSED FOR COOLING.
- DO NOT IMMERSE HEATED PARTS OR ITEMS IN WATER, ALLOW TO COOL NATURALLY.
- USE ONLY BUTANE GAS IN THE PRO-TORCH. DO NOT USE PROPANE GAS OR ANY OTHER TYPES OF FLUIDS.
- DO NOT UNSCREW THE BUTTON IN THE GAS TANK BASE.
- DO NOT STORE IN A TEMPERATURE EXCEEDING 40°C / 104°F.
- KEEP AWAY FROM EYES AT ALL TIMES.
- KEEP THIS UNIT OUT OF THE REACH OF CHILDREN.
- THE FLAME OF THE PRO-TORCH IS NEARLY INVISIBLE IN BRIGHT LIGHT OR SUNLIGHT. MAKE SURE THAT THE GAS FLOW IS TURNED OFF WHEN NOT IN USE.

## INSTRUCTIONS:

- PLEASE READ ALL INSTRUCTIONS AND WARNINGS BEFORE MAKING USE OF THE PRO-TORCH.
- TO FILL GAS TANK, TURN UNIT UPSIDE DOWN AND FIRMLY PUSH THE BUTANE CAN INTO THE FILLING VALVE. THE TANK SHOULD BE FILLED IN APPROXIMATELY TEN SECONDS. PLEASE ALLOW A FEW MINUTES AFTER FILLING FOR THE GAS TO STABILIZE.
- TO IGNITE THE PRO-TORCH, SIMPLY PRESS THE IGNITOR BUTTON. THE SAFETY KILL/OFF SWITCH WILL AUTOMATICALLY POP OUT UPON PRESSING OF THE IGNITOR BUTTON.
- TO SHUT OFF THE PRO-TORCH, YOU NEED ONLY TO REDEPRESS THE KILL SWITCH.
- THE FLAME OF THE PRO-TORCH MAY BE ADJUSTED IN TWO WAYS. YOU MAY INCREASE GAS FLOW AND FLAME LENGTH BY TURNING THE GAS FLOW CONTROL KNOB IN COUNTER-CLOCKWISE DIRECTION. THE FLAME SIZE, LENGTH AND TEMPERATURE MAY ALSO BE ADJUSTED BY CHANGING THE AIRFLOW. TURN THE AIR CONTROL VALVE IN EITHER TO ADJUST THE AIRFLOW.



We love the Earth  
Made in Taiwan